

# Model 145MR

## Current Transformer with Multi-Ratio Window Diameter 6.00"

### Application

Relaying.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

### Frequency

50-400 Hz.

The transformer winding is arranged so that the turns are fully distributed between all taps.

### Insulation Level

600 Volt, 10 kV BIL full wave.

Order mounting bracket kit 0221B00775 separately.

### Model 145MR

Approximate weight 85 lbs.



Catalog Number	Relay Class	Continuous Thermal Rating Factor	
		@ 30 °C	@ 55 °C
145-601MR	C200	2.0	1.5
145-122MR	C400	1.5	1.0
145-202MR	C800	1.33	1.0
145-302MR	C800	1.0	0.8
145-402MR	C800	1.0	0.6
145-502MR	C800	0.8	0.6

