

MODEL 386

Current Transformer

Window Diameter 4.50"



REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Application

Relaying and metering.

Frequency

50-400 Hz.

Insulation Level

600 Volt, 10 kV BIL full wave.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Multi-ratios available on request.

Approximate weight 35 lbs.

Model 386

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	ANSI METERING CLASS AT 60 Hz					SECONDARY WINDING RESISTANCE (Ω @ 75°C)	CONTINUOUS THERMAL RATING FACTOR	
			B0.1	B0.2	B0.5	B0.9	B1.8		@ 30°C	@ 55°C
386-201	200:5	C20	0.6	0.6	1.2	2.4	4.8	0.061	2.0	2.0
386-251	250:5	C20	0.3	0.6	1.2	1.2	2.4	0.077	2.0	2.0
386-301	300:5	C50	0.3	0.3	0.6	1.2	2.4	0.092	2.0	2.0
386-401	400:5	C50	0.3	0.3	0.3	0.6	1.2	0.123	2.0	2.0
386-501	500:5	C50	0.3	0.3	0.3	0.6	0.6	0.153	2.0	2.0
386-601	600:5	C100	0.3	0.3	0.3	0.3	0.6	0.184	2.0	2.0
386-751	750:5	C100	0.3	0.3	0.3	0.3	0.3	0.230	2.0	2.0
386-801	800:5	C100	0.3	0.3	0.3	0.3	0.3	0.245	2.0	2.0
386-102	1,000:5	C100	0.3	0.3	0.3	0.3	0.3	0.307	2.0	1.5
386-122	1,200:5	C200	0.3	0.3	0.3	0.3	0.3	0.368	2.0	1.5
386-152	1,500:5	C200	0.3	0.3	0.3	0.3	0.3	0.502	2.0	1.5
386-162	1,600:5	C200	0.3	0.3	0.3	0.3	0.3	0.535	2.0	1.5
386-202	2,000:5	C200	0.3	0.3	0.3	0.3	0.3	0.669	1.5	1.33

