

MODEL 530

Current Transformer

Window Size 1.88" x 3.06"



REGULATORY AGENCY APPROVALS



Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by U.L. in accordance with IEC 44-1

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30°C. amb., 1.0 at 55°C. amb.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Cast resin construction.


Approximate weight 3.5 lbs.

Excitation data available upon request.

Model 530

CATALOG NUMBER	CURRENT RATIO	ANSI METERING CLASS AT 60 Hz				
		B0.1	B0.2	B0.5	B0.9	B1.8
530-101	100:5	1.2	2.4	—	—	—
530-151	150:5	0.6	1.2	4.8	—	—
530-201	200:5	0.6	1.2	2.4	2.4	—
530-251	250:5	0.3	0.6	1.2	2.4	—
530-301	300:5	0.3	0.6	1.2	1.2	—
530-401	400:5	0.3	0.3	0.6	0.6	—
530-501	500:5	0.3	0.3	0.3	0.6	1.2
530-601	600:5	0.3	0.3	0.6	0.6	1.2
530-751	750:5	0.3	0.3	0.3	0.6	0.6
530-801	800:5	0.3	0.3	0.3	0.6	0.6

Model 530



For more information, visit governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GEA-N50339
English
250917