

# MODEL 594

## Current Transformer

Window Size 8.06"x 20.06"



REGULATORY AGENCY APPROVALS  
 E93779  
 Manufactured to meet the requirements of ANSI/IEEE C57.13.  
 Classified by U.L. in accordance with IEC 44-1

### Application

Relaying.

### Frequency

50-400 Hz.

### Insulation Level

600 Volts, 10 kV BIL full wave.

### Continuous Thermal Current Rating Factor

2.0 at 30 °C. amb., 2.0 at 55 °C. amb.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Approximate weight 150 lbs.


Excitation data available upon request.

### Model 594

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS	DEPTH 'A'
594-500	50:5	C10	4.5
594-750	75:5	C20	5.5
594-101	100:5	C30	5.5
594-151	150:5	C50	5.5
594-201	200:5	C50	5.5
594-301	300:5	C100	5.5
594-401	400:5	C100	5.5
594-501	500:5	C200	5.5



## Model 594 Cast Resin Construction



For more information, visit  
[governova.com/grid-solutions](http://governova.com/grid-solutions)

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.



GE VERNOVA

GEA-N50291  
 English  
 251010