

MODEL JKW-5C

Outdoor Current Transformer

110 kV BIL,
5 to 1,200 A



Application

Designed for outdoor service; suitable for operating meters, instruments, relays and control devices.

Dimensions/Weight

Height: 14.55"

Depth: 12.37"

Width: 10.88"

Weight (Approximate): 66 lbs.

Insulation Level

15.5 kV; BIL: 110 kV per C57.13

Frequency

60 Hz

General Information

JKW-5C are manufactured in ITI's Clearwater, FL. plant utilizing state of the art Automated Pressure Gelation (APG) processes and Hydrophobic Cycloaliphatic Epoxy (HCEP) for the entire line of outdoor voltage transformers. Insulation levels meet or exceed those specified in IEEE C57.13 and CSA CAN3-C13. Dimensions meet IEEE C12.11. Superior designs, HCEP epoxy, and APG processes, are combined to produce the highest quality and reliability available in the industry for outdoor applications.




Model JKW-SC

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS 60 Hz	METERING CLASS 60 Hz	RATING FACTOR
Single Ratio Type JKW-5C 15 kV, 110 kV BIL				
755C150001	5:5	C200	0.3 B-1.8	1.5
755C150002	10:5	C200	0.3 B-1.8	1.5
755C150003	15:5	C200	0.3 B-1.8	1.5
755C150004	20:5	C200	0.3 B-1.8	1.5
755C150005	25:5	C200	0.3 B-1.8	1.5
755C150006	30:5	C200	0.3 B-1.8	1.5
755C150007	40:5	C200	0.3 B-1.8	1.5
755C150008	50:5	C200	0.3 B-1.8	1.5
755C150009	75:5	C200	0.3 B-1.8	1.5
755C150010	100:5	C200	0.3 B-1.8	1.5
755C150011	150:5	C200	0.3 B-1.8	1.5
755C150012	200:5	C200	0.3 B-1.8	1.5
755C150013	300:5	C200	0.3 B-1.8	1.5
755C150014	400:5	C200	0.3 B-1.8	1.5
755C150015	600:5	C200	0.3 B-1.8	1.5
755C150016	800:5	C200	0.3 B-1.8	1.33
755C150017	1,000:5	C150	0.3 B-1.8	1.33
755C150018	1,200:5	C200	0.3 B-1.8	1.5

Model JKW-SC

CATALOG NUMBER	CURRENT RATIO	RELAY CLASS 60 Hz	METERING CLASS 60 Hz	RATING FACTOR
Dual Ratio Type JKW-5C 15 kV, 110 kV BIL				
755C150202	5/10:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150204	10/20:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150207	20/40:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150208	25/50:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150211	75/150:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150212	100/200:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150213	150/300:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150214	200/400:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150215	300/600:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.5
755C150216	400/800:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.33
755C150218	600/1,200:5	C100/C200	0.3 B-0.9 0.3 B-1.8	2.0/1.1

Model JKW-5C



General Construction


- Insulation - Hydrophobic Cycloaliphatic Epoxy (HCEP)
- Baseplate - Heavy gage marine grade aluminum
- Conduit box - Cast aluminum, removable, 1" threaded hubs
- Nameplate - Anodized aluminum
- Mounting - Horizontal, Vertical, Inverted

HCEP Resin Features

- Ideal for outdoor applications
- Excellent water repellent characteristics
- High mechanical properties
- Excellent dielectric properties - stable in outdoor humid conditions
- Enhanced thermal cycle resistance
- High resistance to erosion from ultra violet (UV) radiation High tracking and arc resistance
- Extended service life

Connection Diagram

Available in multiple configurations up to and including: Double



For more information, visit
governova.com/grid-solutions

Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

© 2025 GE Vernova and/or its affiliates. All rights reserved. GE and the GE Monogram are trademarks of General Electric Company used under trademark license.