

# Hydran M2-X



## Enhanced Monitoring with Extended Sensor Life

When a transformer's insulation system is overstressed, the oil and paper undergo chemical degradation producing both hydro-carbon gases and moisture that dissolve into the insulating oil. This increased ageing will shorten the transformer's life, impact its reliability and in some cases can even lead to catastrophic failures.

The Hydran M2-X is the next generation of the field-proven family of Hydran DGA monitoring solutions. It provides continuous monitoring of gas and moisture levels to alert users of developing faults and minimize the risk of unplanned outages. The M2-X builds on GE's strong domain expertise to deliver an optimized, low maintenance monitoring device with an extended sensor life.

### Key Benefits

- Small form factor, no moving parts, low maintenance, and support for APM software analytics, enabling fleet level deployments
- Condition monitoring for a wide range of transformers with mineral insulating oils or ester based fluids (natural and synthetic)
- Extending beyond DGA monitoring, through the connection of sensors, the Hydran M2-X can monitor other parameters such as top oil temperature, load current and through the use of IEEE based mathematical models, can provide further insight on changing transformer conditions
- Providing critical transformer gas behavior data for Asset Performance Management (APM) strategies, facilitating planning of site intervention and maintenance activities
- Supports a wide range of communication methods and protocols to enable easy and secure integration with GE's digital platforms including Perception™ transformer fleet management software, APM software tools, historians and SCADA systems

### Applications

Advanced, flexible and expandable DGA monitoring solution tailored for utility and industrial transformers.

Easily integrates with Kelman multi-gas DGA devices and the Multilin 845 protection & control relay to provide continuous synchronization of chemical and electrical measurements for enhanced transformer monitoring.

## Proven Technology

- Field proven solution, delivering online DGA solutions for over 40 years
- Over 50,000 Hydran units sold worldwide
- Estimated sensor life in excess of 10 years\*
- 7 year product warranty

## Expandable

- Compatible with various transformer oil types (standard mineral insulating oils and newer natural and synthetic ester based fluids)
- Available with the traditional Hydran composite gas (H<sub>2</sub>, CO, C<sub>2</sub>H<sub>2</sub>, C<sub>2</sub>H<sub>4</sub>) sensor or with a discrete Hydrogen only (H<sub>2</sub>) sensor
- Easily upgradable in the field to accept analogue signals to monitor other key transformer parameters
- Computation of winding hot spot and other IEEE transformer models for enhanced diagnostics of the transformer's condition (depending on sensors installed)
- Integrates with Kelman multi-gas DGA devices

## Intuitive

- Easy to install on a single existing transformer valve, often without an outage required
- Integrated display and keypad for simplified local user interaction and data visualization
- Built-in moisture sensor provides water in oil measurement, critical to identifying paper degradation and leaking gaskets
- Compatible with GE's acclaimed Perception™ software to download, trend and analyze transformer health data



# Technical Specifications

## MEASUREMENTS

Fuel cell type sensor behind a gas permeable membrane in contact with transformer insulating oil

<b>Range</b>	25-2000 ppm (volume/volume H <sub>2</sub> equivalent)
<b>Accuracy**</b>	±10 % of reading ±25 ppm
<b>Response time</b>	10 minutes (90 % of step change)

### "Composite Gas" Sensor

<b>Relative sensitivity</b>	H <sub>2</sub> : 100 % of concentration CO: 15 ± 4 % of concentration C <sub>2</sub> H <sub>2</sub> : 8 ± 2 % of concentration C <sub>2</sub> H <sub>4</sub> : 1.5 ± 0.5 % of concentration
<b>Repeatability</b>	Highest of ±5 % of reading or ±5 ppm

### "Discrete H<sub>2</sub>" Gas Sensor (Mineral oil only)

<b>Relative sensitivity</b>	H <sub>2</sub> : 100 % of concentration Interference from CO, C <sub>2</sub> H <sub>2</sub> and C <sub>2</sub> H <sub>4</sub> less than 3 % of concentration
<b>Repeatability</b>	Highest of ±5 % of reading or ±10 ppm

### Moisture Sensor

Thin film capacitive type sensor immersed in insulating oil

<b>Range</b>	0-100 % RH
<b>Accuracy</b>	± 2 % RH
<b>Repeatability</b>	± 2 % RH

## FEATURES

### Display

Backlit LCD, 128 x 64 pixels

Keypad to setup unit and acknowledge alarms

## Communications

Standard RS-232 port (DB-9 connector), for local connection to computer for configuring the system

Standard RS-485 (terminal block), isolated to 2000Vac RMS, for remote communication or connection to local Hydran network  
Optional: TCP/IP over Ethernet Copper or Fiber Optic 10/100Mbps/s

### Protocols

Standard: Modbus®, DNP 3.0  
Optional: IEC 61850 over TCP/IP

### Alarms

Gas and Moisture Alert (Hi), Gas and Moisture Alarm (HiHi), System Alarms

Gas alarms can be set on gas level reached or on hourly or daily trend (gas level rate of change)

Moisture alarms can be set on level reached or average level

Alarms can also be configured for optional additional analogue inputs or for calculation results from optional transformer models

5 dry contact relays (type C, SPDT), NO/NC, 3A@250Vac resistive load, 3A@30Vdc resistive load

### Manual Sampling

Easily accessible external oil sampling port, for use with glass syringe with Luer stopcock

## ENVIRONMENT

### Conditions

**Operating ambient temperature** -40 °C to +55 °C (-40 °F to +131 °F)

**Operating ambient humidity** 0-95 % RH, non-condensing

**Oil temperature at valve** -40 °C to +105 °C (-40 °F to +221 °F) with finned heat sink adaptor option

**Oil pressure at valve** 0-700KPa (0-100psi)  
Vacuum resistant sensor

## Enclosure

Material: Aluminum  
Rating: NEMA Type 4X certified, meets requirements of IP56

### Power Requirements

90-132 Vac or 180-264 Vac switch mode universal power supply, 47-63 Hz, 650VA max

### Mechanical

Has a 1.5" NPT male thread, can mount on 1.5" NPT valve or greater using optional adaptors

**Dimensions** 315 x 219 x 196 mm  
12.4 x 8.63 x 7.72"

**Installed weight** 7.5 Kg (16.5 lb)

**Shipping weight** 9.0 Kg (20 lb)

### PRODUCT OPTIONS & SENSORS

Finned heat sink adaptor (1.5") for use when ambient temp > 40 °C (104 °F) or oil temp > 90 °C (194 °F).

Valve adaptors 2" to 1.5"

Transformer models calculations (for mineral oil only)

Analogue input cards, 4-20mA, 10V load max, isolated to 2000Vac RMS

Dual digital input cards for dry contacts, internal wetting 24Vdc, isolated 2000Vac

Analogue output cards, 4-20mA, 10V load max, isolated to 2000Vac RMS

PSTN analogue modem V92/56K

GSM/GPRS wireless modem

Network Ethernet communication using copper or multimode fiber optic (ST)

Oil temperature sensor, magnetic mount, (4-20mA)

Split core load CT (4-20mA)

Ambient temperature sensor (4-20mA)

Anodized Aluminum Enclosure - CRC required (minimum quantities applicable)

Hydran M2X	-	Ox	Sx	Ax	Bx	Cx	Dx	Px	Gx	VCx	Vx	Ex	Mx	Lx	Selection Description	
Oil type		O1 NE SE													Mineral Oil Natural Ester Oil (CRC Required) Synthetic Ester Oil	
Sensor type			S1 H2												Composite gas sensor Hydrogen only sensor	
Card slot A,B,C,D				A0 A1 A2 A3	B0 B1 B2 B3	C0 C1 C2 C3	D0 D1 D2 D3								No analogue card Analogue Input card, 4-20mA Analogue Output card, 4-20mA Digital dual input card	
Communication Protocol Options								P0 P1 P2 P3 P4 P5							Modbus/DNP 3.0 over RS 232/RS 485 Standard Modbus/DNP 3.0 over TCP/IP Ethernet Card wired connection, 10/100 Mbps/s Modbus/DNP 3.0 over TCP/IP Ethernet MM Fibre, ST connectors, 10/100 Mbps/s Modbus/DNP 3.0 over PSTN Analog Modem Modbus/DNP 3.0 over GPRS/3G/4G Wireless Modem External Option (CRC Required) IEC-61850 Protocol over TCP/IP, with RJ45 Connector (CRC Required)	
Valve Type									G0 G1						Installation on gate valve (standard) Installation on globe valve	
Valve Connection										VC0 VC1 VC2					Standard Connection - 1.5" Male NPT Valve adaptor 2" Male NPT to 1.5" Female NPT Valve adaptor 1" Male NPT to 1.5" Female NPT	
Heat Finned Adaptor											V0 V1				No Finned Heat-Skin Adaptor Finned Heat-Skin Adaptor - 1.5" Male NPT	
Enclosure												E0			Aluminum - Standard	
Transformer Models													M0 M1		No Transformer Models Transformer Models Enabled (Requires additional sensors)	
Language															L0 L1 L2 L3 L4	English labels and manuals French labels and manuals Spanish labels and manuals German labels and manuals Russian labels and manuals

\*Fuel cell sensor life projection based on accelerated aging test showing estimated MTTF of 11.5 years

\*\*Accuracy is quoted for the sensors at calibration, for H<sub>2</sub> equivalent performance

GE Grid Solutions  
Lissie Industrial Estate East  
Unit 1, 7 Lissie Walk  
Lisburn BT28 2LU  
United Kingdom  
Tel: +44 (0) 2892 622915

[GEGridSolutions.com](http://GEGridSolutions.com)

GE, the GE Monogram, Hydran and Perception are trademarks of the General Electric Company.

Modbus is a registered trademark of Schneider Automation, Inc. IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers Inc. IEC is a registered trademark of Commission Electrotechnique Internationale.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes.

© Copyright 2022, General Electric Company. All Rights Reserved.

HydranM2-X-Brochure-EN-2022-12-Grid-GA-1644



For further information scan here

