

# Model 2DARL

## Current Transformer Window Diameter 1.00"

### Application

Ammeters , wattmeters and cross current compensation.

### Rating Factor

1.0 @ 30°C. amb.

### Frequency

50-400 Hz

### Insulation Level

600 Volts, 10 kV BIL full wave

Flexible leads are UL 1015, 105 °C, CSA approved, #16 AWG, 24" long. Non-standard, lead length can be specified.

Approximate weight 0.9 lbs.



#### REGULATORY AGENCY APPROVALS





Manufactured to meet the requirements of ANSI/IEEE C57.13.  
Classified by U.L. in accordance with IEC 44-1

### Data Table

Catalog number	Current Ratio	V.A. ±1% Class	ANSI Metering Class at 60 HZ			Secondary Winding Resistance (Ω@75 °C)
			B0.1	B0.2	B0.5	
2DARL-500	50:5	2% 2.5	4.8	—	—	0.008
2DARL-600	60:5	2.5	2.4	—	—	0.011
2DARL-750	75:5	3.5	1.2	2.4	—	0.015
2DARL-800	80:5	4.0	1.2	2.4	—	0.016
2DARL-101	100:5	5.0	1.2	2.4	—	0.018
2DARL-121	120:5	5.0	1.2	2.4	—	0.022
2DARL-1250	125:5	5.0	0.6	1.2	—	0.028
2DARL-151	150:5	10.0	0.6	0.6	—	0.031
2DARL-201	200:5	12.5	0.3	0.6	1.2	0.047
2DARL-251	250:5	15.0	0.3	0.3	0.6	0.074
2DARL-301	300:5	20.0	0.3	0.3	0.6	0.089



# Model 2DARL



[GEGridSolutions.com](http://GEGridSolutions.com)

Grid-AIS-L4-ITL\_Model\_2DARL-1188-2017\_05-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

**Worldwide Contact Center**

Web: [www.GEGridSolutions.com/contact](http://www.GEGridSolutions.com/contact)

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

