GE Grid Solutions



MS 3000

Holistic Transformer Monitoring Solution

Faced with increasing pressure to continuously improve network availability and reliability, asset owners are now often looking for increased coverage on their important transformers. Continuously monitoring the transformer's main components (active part, bushings, tap changer, cooling system) is key to maximizing transformer availability, reliability and performance while reducing the life-cycle cost. Asset owners are therefore expanding beyond Dissolved Gas Analysis (DGA) and connecting to or adding more sensors to extend their online monitoring reach.

GE'S MS 3000 holistic and modular transformer monitoring system enables essential to comprehensive coverage of the most common causes of failure. It lets you combine the outputs of available sensors to form a homogeneous data flow coming from a single source. It uses analysis and sophisticated models to prevent data overload and deliver an aggregate view of the health of the transformer's main components, providing intelligent alarms, diagnostics and suggested operational next steps. The MS 3000 is an "Expert System" which helps you confidently assess a transformer's condition and optimize its operation and maintenance.

Key Benefits

- Continuous supervision of the whole transformer, integrating data from available sensors
- Modular: essential through to comprehensive coverage of transformer failure modes
- All information available at a glance, even across several substation transformers
- An "Expert System" to help you assess and manage your costly assets
- Optimum operation efficiency with reduced life-cycle cost
- Web server HMI, no need for software to access the data analysis
- Integration with GE's Perception software for centralised information and leveraging of fleet data**
- Easy inter-operability of the transformer with the Smart Grid / Digital Substation

Applications

While more specifically aimed at transformer assets where the loss of availability has severe consequences for the network, the MS 3000 benefits from a highly flexible and modular design enabling it to adapt to a wide range of customer demands and types of applications:



- Suitable for most transformer types and ratings, independent of manufacturer
- Applicable to new and existing transformers
- Used in power generation, transmission and distribution
- Special solutions for HVDC applications
- Ideal for industries with process interruption risks

Dissolved Gas Analysis

 Combines with any GE or other DGA monitor and provides even more powerful diagnostics by correlating with load and temperature

Active Part Supervision

- A transformer's active part (e.g. core, winding, insulation, leads) has a finite design life
- Extending it requires detecting stress situations causing premature degradation and correcting them

Bushing Monitoring

- Bushing failures represent approximately 17% of sub-station transformer failures*
- Many of these are "catastrophic" leading to total loss of the transformer with significant additional collateral damage

Cooling System

- Common causes of overheating (like nonfunctioning fans) can easily be detected
- Cooling efficiency can be improved

On Load Tap Changer

- When present, OLTC, can account for up to 26% of sub-station transformer failures*
- The regular maintenance of frequently working OLTCs can also be optimized

Electrical Stress Detection

 Partial discharge and transient over-voltages can erode/damage solid insulation if not detected and removed or attenuated

Decision Aids

- Transformer health status report can quickly and easily be produced using report generator
- Built-in simulator lets you understand the implications of external or internal events



Expert System

Algorithms for analyzing the data acquired online are implemented in the software and reflect GE's extensive experience with transformers. The expert system highlights issues through configurable alarms and provides clear correlated information as well as recommendations concerning the transformer continued operation, the suggested "next steps" and the need for service/maintenance.



Load

- Load currents (A)
- Over-currents (A)
- Total number of over-currents (A)
- Load factor (A)
- Overload capacity (A)
- Emergency overloading time (A)
- Apparent power (A)
- Active power
- Reactive power
- Transformer power factor (cos φ)
- Transformer losses

Dissolved Gas Analysis

- Gas in oil content (1 to 9 gases) (A)
- Gas in oil rate of change (A)
- Moisture in oil content (A)
- DGA in OLTC

A modular and configurable system that can monitor the various key components of a power transformer listed here, depending on the asset owner's requirements.

On Load Tap Changer

- OLTC position (A)
- Number of switching operations (A)
- Number of operations until service (A) Contact erosion
- Cum. switched load current (A)
- Cum. current until service (A)
- Power consumption of motor drive (B) Oil temperature
- Motor drive current
- Operation timing (B)

- Assessed mechanical condition (B)
- Energy index (B)
- Gas in oil content
- Moisture in oil content
- Oil temperature differences
- Oil level in OLTC

- - Cabinet temperature

Environment

- Ambient temperature (A)

Ambient humidity

With a multitude of sensors constantly delivering refreshed online data, the MS 3000 uses sophisticated models to analyse all this data, correlate it when additional sources are available and convert the data enable the asset owner to get the most out of the transformer.

Bushings

- Top oil temperature (A) • Operating voltages (C)
- Bottom oil temperature
- Calculated hot spot temperature (A)
- Winding temperature

Insulation

- Moisture in insulation paper (A)
- Bubbling temperature (A)
- Bubbling safety margin (A) • Breakdown voltage (A)
- Lifetime consumption (A)
- Ageing rate (A)

- Transient lightening over-voltages (C)
- Total number of over-voltages (C)
- Change of C1 capacitance (C)
- Power factor (tan δ)

Other measures

Oil pressure

• Oil level in main tank

• Humidity of air inside conservator

• Other digital and analogue inputs

• Other parameters on request

Simulator

• Gas auantity/aradient in Buchholz relay

• Oil/SF6 pressure/density

Transient Over-Voltage

- Detection of fast transient over- voltages (up to 5 MHz) caused by network switching
- Capture of full waveform

Partial Discharge

- Electrical PD
- UHF PD



Letters (A). (B) or (C) indicate inclusion in the various standard configuration kits, see back page for details.

Cooling System

- Operating condition of individual/group fans and pumps (A)
- Operating time of individual/group fans and pumps (A)
- Cooling efficiency (Rth) (A)
- Cooling power
- Inlet and outlet cooling system temperatures
- Difference of inlet & outlet temperatures
- Oil/water flow
- Current consumption of individual/group fans and pumps
- Intelligent cooling control for conventional and speed controlled fans

Report Generator

The configurable report generator quickly and easily creates a user-friendly report on the status of the transformer and of its main components. The report can be created on demand for selected monitored functions over a specified time frame.

НМІ

which can be accessed using a standard web browser. The key data overview screen will highlight any alarm and enable to drill of a transformer fleet, integration with GE's Perception software** enables centralised information, leveraging of fleet data and fleet health ranking.



Sophisticated Modelling

The built-in simulator module allows the transformer events and to study the corresponding effect on the transformer's behavior. It can be invaluable for weighing decision but can also be used for training of

GEGridSolutions.com GEGridSolutions.com


Modular monitoring solution for power transformers

The MS 3000 is a globally recognized online monitoring solution with well over 1,000 installations worldwide which benefits from extensive transformer manufacturing DNA. It is a powerful tool that concentrates most of the transformer data available and combines it with sophisticated models, diagnostic algorithms and practical experience to help the user evaluate the health of the transformer, monitor its current performance and optimize its operational efficiency.

The MS 3000 is modular and highly configurable so that it can accommodate a wide range of specifications or customer requirements surrounding monitoring of the 6 main areas responsible for the failure of power transformers. Standard configurations are also available to cover typical requirements.

Its wide range of communication options facilitates connection to SCADA systems, data historians and Asset Performance Management (APM) systems.

All this is provided by a single vendor with extensive transformer manufacturing and monitoring experience, which supports the customer from conception to deployment, ensures that the solution meets expectations and stands by it for the long term.



Technical Specifications

CUSTOMIZED SOLUTION

Flexible System

- · Fully configurable system to meet wide set of specifications
- Scalable addition of sensors and functionalities
- Flexible architecture to meet site requirements
- Ability to integrate existing sensors and monitors
- Working with all transformer designs and makes

Implementation support

- Detailed review of suitable options
- Advice on sensor requirement and positioning
- Optional planning site visit
- Solution project management

Successful delivery

- Extensive testing of solution prior to shipping
- Commissioning on site
- Training of personnel
- Global service support

STANDARD CONFIGURATIONS

Kit 1 - Base Module (A)

- Dissolved Gas Analysis
- Load
- Insulation
- Environment
- Cooling System Basic OLTC

Kit 2 – Base Module + Extended OLTC (A+B):

- · Features of "Base Module
- Extended OLTC monitoring

Kit 3 - Base Module + Bushing (A+C):

- · Features of "Base Module"
- Bushing monitoring

Kit 4 – Base Module + Bushing + Extended OLTC (A+B+C):

- Features of "Base Module"
- Bushing monitoringExtended OLTC monitoring

Specific content indicated in centre page by letter coding

Modular Sensors and monitoring capabilities as required

Reliability Fan-less, robust design for on-transformer installation

Lifetime data managemen using solid state disc (SSD). Data ent and storage,

нмі Built-in Web server, available in several

Communications Wide range of communication interfaces. IEC® 60870-5-101/104, Modbus®, DNP3, IEC 61850 **Protocols**

Operating -40°c to +55°C -40°F to +131°F temperature 95% non condensing Operatina humidity **Enclosure rating** IP 55 standard, IP 66 optional

Power requirements 100 - 240 Vac 50/60 Hz 85 - 375 Vdc

Dimensions

 $600\times600\times250~mm$ (23.6" \times 23.6" \times 9.8") for small enclosure used in standard kits.

Up to $600 \times 1200 \times 300$ mm (23.6" \times 47.2" \times 11.8" for enclosure of large customized

From 30 to 100 Kg (66 to 220 lb) depending on configuration Weiaht

* Source: Cigré WG A2.37 ** Coming soon in 2016

> GE Grid Solutions Lissue Industrial Estate East Unit 1. 7 Lissue Walk Lisburn BT28 2LU United Kingdom Tel: +44 (0) 2892 622915

GEGridSolutions.com

Modbus is a registered trademark of Schneider Automation Inc., IEC is a registered trademark of Commission Electrotechnique Internationale, IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers Inc. Cigré is a registered trademark of Conseil International des Grands Réseaux Electriques.

GE reserves the right to make changes to specifications of products described at any time without notice and without obligation to notify any person of such changes. GEA-31984

English 160614 Copyright 2016, General Electric Company

