

Model 307MR

Current Transformer with Multi-Ratio Window Diameter 4.50"

Application

Relaying.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Frequency

50-400 Hz.

The transformer winding is arranged so that the turns are fully distributed between all taps.

Insulation Level

600 Volt, 10 kV BIL full wave.

Order mounting bracket kit 0221B01525 separately.

Approximate weight 53 lbs.


REGULATORY AGENCY APPROVALS




Manufactured to meet the requirements of ANSI/IEEE C57.13. Classified by U.L. in accordance with IEC 44-1

Model 307MR

Catalog Number	Relay Class	Continuous Thermal Rating Factor	
		@ 30 °C	@ 55 °C
307-601MR	C200	2.0	1.5
307-122MR	C400	1.5	1.33
307-202MR	C800	1.33	1.0
307-302MR	C800	1.0	0.8



Model 307MR



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_307MR-1291-2017_05-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

