

GE

Energy Connections

Model 560

Current Transformer
Window Size 3.25" x 4.25"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Insulation System

Temperature Class H (180 °C).

Continuous Thermal Current Rating Factor

1.33 at 30 °C. amb., 1.0 at 55 °C. amb.

Terminals are brass studs No. 10-32 with one flatwasher, lockwasher and regular nut.

Approximate weight 6 lbs.



REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1



Model 560

Catalog Number	Current Ratio	ANSI Metering Class at 60 Hz					Secondary Winding Resistance (Ω @ 75 °C)
		BO.1	BO.2	BO.5	BO.9	B1.8	
560-101	100:5	2.4	—	—	—	—	0.012
560-151	150:5	1.2	2.4	—	—	—	0.017
560-201	200:5	1.2	1.2	—	—	—	0.023
560-251	250:5*	0.6	1.2	2.4	—	—	0.038
560-301	300:5*	0.6	0.6	1.2	—	—	0.045
560-401	400:5*	0.6	0.6	1.2	2.4	—	0.095
560-501	500:5*	0.3	0.3	0.6	1.2	2.4	0.118
560-601	600:5*	0.3	0.3	0.6	1.2	1.2	0.142
560-751	750:5*	0.3	0.3	0.3	0.6	1.2	0.178
560-801	800:5*	0.3	0.3	0.3	0.6	0.6	0.190
560-102	1,000:5*	0.3	0.3	0.3	0.6	0.6	0.211
560-122	1,200:5*	0.3	0.3	0.3	0.3	0.6	0.253
560-152	1,500:5*	0.3	0.3	0.3	0.3	0.6	0.368
560-162	1,600:5*	0.3	0.3	0.3	0.3	0.6	0.262
560-202	2,000:5*	0.3	0.3	0.3	0.3	0.6	0.328
560-252	2,500:5*	0.3	0.3	0.3	0.3	0.3	0.410
560-302	3,000:5*	0.3	0.3	0.3	0.3	0.3	0.347
560-322	3,200:5*	0.3	0.3	0.3	0.3	0.3	0.370
560-402	4,000:5*	0.3	0.3	0.3	0.3	0.3	0.462

Approved for revenue metering by Industry Canada No. AE-0659 (*)



Model 560



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_560-1321-2017_05-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

