

Model 571

Current Transformer
Window Size 3.58" x 4.13"

Application

Metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Continuous Thermal Current Rating Factor

1.33 at 30 °C. amb.,
1.0 at 55 °C. amb.

Terminals are brass studs No. 10-32
with one flatwasher, lockwasher and
regular nut.

Approximate weight 4 lbs.





REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Model 571

Catalog Number	Current Ratio	ANSI Metering Class at 60 Hz					Secondary Winding Resistance (Ω @ 75 °C)
		BO.1	BO.2	BO.5	BO.9	B1.8	
571-801	800:5	0.6	0.6	0.6	1.2	2.4	0.143
571-102	1,000:5	0.3	0.3	0.6	0.6	1.2	0.179
571-122	1,200:5	0.3	0.3	0.6	0.6	1.2	0.215
571-152	1,500:5	0.3	0.3	0.3	0.6	0.6	0.337
571-162	1,600:5	0.3	0.3	0.3	0.6	0.6	0.360
571-202	2,000:5	0.3	0.3	0.3	0.3	0.6	0.497
571-252	2,500:5	0.3	0.3	0.3	0.3	0.3	0.622
571-302	3,000:5	0.3	0.3	0.3	0.3	0.3	0.746
571-322	3,200:5	0.3	0.3	0.3	0.3	0.3	0.872



Model 571



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_571-1330-2017_06-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

