

GE

Energy Connections

Model 3P528

Current Transformer
Window Size 2.33" x 5.20"

Application

3 phase metering.

Frequency

50-400 Hz.

Insulation level

600 Volts, 10 kV BIL full wave.

The core and coil assembly is encased in a thermoplastic shell and filled with resin.

Terminals are brass screws No. 10-32 with one flatwasher.

Approximate weight 12 lbs.





REGULATORY AGENCY APPROVALS
 
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Data Table: Model 3P528

Catalog Number	Current Ratio	ANSI Metering Class at 60 Hz					Secondary Winding Resistance (OHMS @ 75°C)
		BO.1	BO.2	BO.5	BO.9	B1.8	
3P528-101	100:5	4.8	—	—	—	—	0.020
3P528-201	200:5	1.2	2.4	4.8	—	—	0.035
3P528-251	250:5	1.2	2.4	4.8	—	—	0.043
3P528-301	300:5	0.6	1.2	2.4	4.8	—	0.062
3P528-401	400:5	0.3	0.6	1.2	2.4	—	0.079
3P528-501	500:5	0.3	0.3	1.2	2.4	—	0.104
3P528-601	600:5	0.3	0.3	0.6	1.2	2.4	0.125
3P528-751	750:5	0.3	0.3	0.6	0.6	1.2	0.163
3P528-801	800:5	0.3	0.6	0.6	0.6	1.2	0.209
3P528-102	1000:5	0.3	0.3	0.6	0.6	1.2	0.261
3P528-122	1200:5	0.3	0.3	0.3	0.6	0.6	0.313



Model 3P528



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_3P528-1197-2017_05-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

