

Models JVM-5A

Indoor Voltage Transformer
4,200 V to 14,400 V, BIL 75 kV to 110 kV, 60 Hz



JVM-5A Voltage Transformer
(two-fuse design)

Application

Designed for indoor service; suitable for operating meters, instruments, relays, and control devices.

Regulatory Agency Approvals

UL RecognizedFile E178265

Thermal Rating (Volt-Amperes)

55 °C Rise above 30 °C Ambient2,000
30 °C Rise above 55 °C Ambient1,400

Weight (Approximate in Pounds)

Unfused105/85
Fused110/90

Reference Drawings

Accuracy Curve 9932600137
Excitation Curves:
JVM-5A9932600139

JVM-5A (two-fuse design)

Line-To-Line Circuit Voltage for Permissible Primary Connection			Transformer Rating (1)		Accuracy Classification 60 Hz		BIL	Catalog Number	Primary Fuse Ratings	
Δ	Y	Y Only	Primary Voltage	Ratio	ACCUBUTE	ANSI			Amps	Volts
Unfused - JVM-5A										
7,200	7,200	12,470	7,200	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023001	---	---
7,620	7,620	13,200	7,620	63.5:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023002	---	---
8,400	8,400	14,400	8,400	70:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023003	---	---
12,000	12,000	---	12,000	100:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023004	---	---
13,200	13,200	---	13,200	110:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023005	---	---
14,400	14,400	---	14,400	120:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023006	---	---
One Primary Fuse - JVM5A										
---	---	7,200	7,200 ⁽⁵⁾	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023010	1 A	7,200
---	---	12,470	7,200	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023011	1 A	14,400
---	---	7,620	7,620	63.5:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023012	1 A	14,400
---	---	8,400	8,400	70:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023013	1 A	14,400
---	---	12,000	12,000	100:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023014	0.5 A	14,400
---	---	13,200	13,200	110:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023015	0.5 A	14,400
---	---	14,400	14,400	120:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z (2)	110 kV	765X023016	0.5 A	14,400
Two Primary Fuses - JVM-5A										
7,200	---	7,200 ⁽⁴⁾	7,200	60:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023020	1 A	7,200
12,000	---	12,000 ⁽⁴⁾	12,000	100:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023024	0.5 A	14,400
13,200	---	13,200 ⁽⁴⁾	13,200	110:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023025	0.5 A	14,400
14,400	---	14,400 ⁽⁴⁾	14,400	120:1	0.15 W, X, M, Y	0.3 W, X, M, Y, Z	110 kV	765X023026	0.5 A	14,400

Notes:

(1) For continuous operation, the transformer-rated primary voltage should not be exceeded by more than 10%. Under emergency conditions, over-voltage must be limited to 1.25 times the transformer primary voltage rating.

(2) ANSI 69 Volt burden.

(3) This transformer is similar to Catalog Number 764X021011 except for the voltage rating of the fuse.

(4) For Y connections, it is preferred practice to connect one lead from each voltage transformer directly to the grounded neutral, using a fuse only in the line side of the primary.

By this connection a transformer can never be "alive" from the line side by reason of a blown fuse on the grounded side.

(5) This transformer is similar to Catalog Number 765X023011 except for the voltage rating of the fuse.



Indoor – Voltage – JVM-5A

Reference Drawings (con't)

Accessories Catalog Number

Fuses, Current-limiting, Type EJ-1:

4,800 Volt Class, 1 Ampere	9F60BDD001
4,800 Volt Class, 2 Ampere	9F60BDD002
7,200 Volt Class, 1 Ampere	9F60BDE001
7,200 Volt Class, 2 Ampere	9F60BDE002
14,400 Volt Class, 0.5 Ampere	9F60BHH905

Construction and Insulation

Please refer to General Product Information, item 1.4.

Core

Please refer to General Product Information, item 2.3.

Primary and Secondary Coils

Please refer to General Product Information, item 3.2.

Primary Terminals

Please refer to General Product Information, item 4.2.

Fuses

Current-limited, Type EJ-1 fuses are used.

Secondary Terminals

Please refer to General Product Information, item 4.12.

Polarity

Please refer to General Product Information, item 7.2.

Baseplate and Mounting

Please refer to General Product Information, item 5.6.

Nameplate

Please refer to General Product Information, item 6.5.

Maintenance

Please refer to General Product Information, item 10.1 and pages 24-27.



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_JVM_5A-1496-2017_07-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00