

Model 450I

Voltage Transformer IEC Rated 50 Hz

Application

50 Hz.

Standard Secondary Voltage

110 Volts.

Insulation Level

0.72 kV

Accuracy Class:

0.2 @ 40 VA

0.5 @ 70 VA

Thermal Rating:

550 VA at 30 °C. amb.,
350 VA at 55 °C. amb.

The primary and secondary terminals are No. 10-32 screws into 3/8" deep brass inserts and fitted with one lockwasher and flatwasher and are contained in a sealable terminal cover.

Approximate weight 11.4 kg



No Fuse



Retro Fit Fuse Kit Order No. 0222 PL 7019



1 Fuse



2 Fuses



Clear Plastic Cover

Model 450I

Not fused*	Catalog Number		Voltage Rating	Turns Rating	Rec. Primary Fuse rating
	Primary Fuses Only	Primary and Secondary Fuses			
450I-110	450I-110F	450I-110FF	110:110	1:1	10 amp.
450I-220	450I-220F	450I-220FF	220:110	2:1	6 amp.
450I-380	450I-380F	450I-380FF	380:110	3.45:1	3 amp
450I-400	450I-400F	450I-400FF	400:110	3.64:1	3 amp
450I-416	450I-416F	450I-416FF	416:110	3.78:1	3 amp
450I-440	450I-440F	450I-440FF	440:110	4:1	3 amp


Above part numbers are available with 100 volt secondaries.

*CE marking applies to non-fused models



Model 450I

- The core and coil assembly is encased in a thermoplastic shell and filled with resin.
- These transformers are designed for operation line-to-line. They may also be operated line-to-ground or line-to-neutral at reduced voltage, (58% of rated volts).
- It is desirable to use a 6.0 amp BBS type or equal fuse in the secondary to protect the transformer.
- When primary fuses are requested, the rating will be as given in the table.
- When only one fuse is used, it must be connected into the line side (P1) terminal wiring. This will prevent the presence of voltage at the P1 terminal for a ruptured fuse in the neutral (P2) terminal wiring for line-to-neutral connected transformers.



Dimensions in millimeters.

GEGridSolutions.com

ITI-Model-450I-Specs-EN-2021-03- Grid-AIS-1149. © Copyrights 2021 General Electric. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

