

Multilin Agile

P14D, P14N, P94V

PICS
Protocol Implementation Conformance - IEC 61850 Edition 2

Software version: 06
Publication reference: MuAgile-PC2-EN-5



CONTENTS

1	Protocol Implementation Conformance Statement (PICS)	3
1.1	Introduction	3
1.2	ACSI Basic Conformance Statement	3
1.3	ACSI Models Conformance Statement	3
1.4	ACSI Service Conformance Statement	5

1 PROTOCOL IMPLEMENTATION CONFORMANCE STATEMENT (PICS)

1.1 INTRODUCTION

This specification is the Protocol Implementation Conformance Statement (PICS) and presents the ACSI conformance statements as defined in Annex A of Part 7-2 of the IEC 61850 standard specifications.

This document is applicable for Multilin Agile range products (P14N, P14D and P94V) with firmware version 06 and IEC 61850 version 6.

Note:

This range is undergoing a transition, with 30TE models being branded as Multilin Agile, whereas the 20TE model carries P40 Agile Enhanced branding for a transition period. Both 20TE and 30TE products are similar, with any differences between them highlighted by reference to the case size. For more information refer to instruction manual MAP14-TM-EN-5.pdf on the Grid Solutions web page.

1.2 ACSI BASIC CONFORMANCE STATEMENT

The basic conformance statement is defined in Table 1.

Client-Server Roles		Client/ Subscriber	Server/ Publisher	Value/ Comments
B11	Server side (of TWO-PARTY-APPLICATION-ASSOCIATION)		Y	
B12	Client side of (TWO-PARTY-APPLICATION-ASSOCIATION)			
SCSMs supported				
B21	SCSM: IEC 6185-8-1 used		Y	
B22	SCSM: IEC 6185-9-1 used			Ed2: Deprecated
B23	SCSM: IEC 6185-9-2 used			
B24	SCSM: other			
Generic substation event model (GSE)				
B31	Publisher side		Y	
B32	Subscriber side	Y		
Transmission of sampled value model (SVC)				
B41	Publisher side			
B42	Subscriber side	Y		
–				
Y = supported				
N or empty = not supported				

Table 1: Basic conformance statement

1.3 ACSI Models Conformance Statement

The ACSI models conformance statement is defined in Table 2.

Client-Server Roles		Client/ Subscriber	Server/ Publisher	Value/ Comments
If Server or Client side (B1) is supported				
M1	Logical Device	Y		
M2	Logical Node	Y		
M3	Data	Y		
M4	Data set		Y	

Client-Server Roles		Client/ Subscriber	Server/ Publisher	Value/ Comments
M5	Substitution			
M6	Setting group control			
	Reporting			
M7	Buffered report control		Y	
M7-1	sequence-number		Y	
M7-2	report-time-stamp		Y	
M7-3	reason-for-inclusion		Y	
M7-4	data-set-name		Y	
M7-5	data-reference		Y	
M7-6	buffer-overflow		Y	
M7-7	entryID		Y	
M7-8	BuTim		Y	
M7-9	IntgPd		Y	
M7-10	GI		Y	
M7-11	conf-revision		Y	
M8	Unbuffered report control		Y	
M8-1	sequence-number		Y	
M8-2	report-time-stamp		Y	
M8-3	reason-for-inclusion		Y	
M8-4	data-set-name		Y	
M8-5	data-reference		Y	
M8-6	BuTim		Y	
M8-7	IntgPd		Y	
M8-8	GI		Y	
M8-9	conf-revision		Y	
	Logging			
M9	Log control			
M9-1	IntgPd			
M10	Log			
M11	Control		Y	
M17	File Transfer		Y	
M18	Application Association		Y	
M19	GOOSE Control Block		Y	
M20	Sample Value Control Block			
If GSE (B31/32) is supported				
M12	GOOSE	Y	Y	
M13	GSSE			Deprecated
If SVC (41/42) is supported				
M14	Multicast SVC			
M15	Unicast SVC			
For all IEDs				
M16	Time	Y	Y	
Y = service is supported				
N or empty = service is not supported				

Table 2: Basic conformance statement

1.4 ACSI Service Conformance Statement

The ACSI service conformance statement is defined in Table 2 (depending on the statements in Table 1).

	Ed.	Services	AA: TP/MC	Client (C)	Server (S)	Comments
Server						
S1	1, 2	GetSeverDirectory(LOGICAL-DEVICE)	TP		Y	
Application Association						
S2-1	1, 2	Associate Request	TP			
S2-2		Associate Response			Y	
S3-1	1, 2	Abort Request	TP			
S3-2		Abort Processing			Y	
S4-1		Release Request				
S4-2	1, 2	Release Response	TP		Y	
Logical Device						
S5	1, 2	GetLogicalDeviceDirectory	TP		Y	
Logical Node						
S6	1, 2	GetLogicalNodeDirectory	TP		Y	
S7	1, 2	GetAllDataValues	TP		Y	
Data						
S8	1, 2	GetDataValues	TP		Y	
S9	1, 2	SetDataValues	TP		Y	
S10	1, 2	GetDataDirectory	TP		Y	
S11	1, 2	GetDataDefinition	TP		Y	
Data Set						
S12	1, 2	GetDataSetValues	TP		Y	
S13	1, 2	SetDataSetValues	TP			
S14	1, 2	CreateDataSet	TP			
S15	1, 2	DeleteDataSet	TP			
S16	1, 2	GetDataSetDirectory	TP		Y	
Substitution						
S17	1	SetDataValues	TP			
Setting Group Control						
S18	1, 2	SelectActiveSG	TP			
S19	1, 2	SelectEditSG	TP			
S20	1, 2	SetSGValues	TP			
S21	1, 2	ConfirmEditSGValues	TP			
S22	1, 2	GetSGValues	TP			
S23	1, 2	GetSGCBValues	TP			

	Ed.	Services	AA: TP/MC	Client (C)	Server (S)	Comments
Reporting						
Buffered Report Control Block (BRCB)						
S24		Report	TP		Y	
S24-1	1, 2	data-change (dchg)			Y	
S24-2	1, 2	qchg-change (qchg)			Y	Partially implemented: • Test bit when the unit is set in Test Mode • OutOfRange for metering
S24-3	1, 2	data-update (dupd)				
S25	1, 2	GetBRCBValues	TP		Y	
S26	1, 2	SetBRCBValues	TP		Y	
Unbuffered Report Control Block (URCB)						
S27		Report	TP		Y	
S27-1	1, 2	data-change (dchg)			Y	
S27-2	1, 2	qchg-change (qchg)			Y	Partially implemented: • Test bit when the unit is set in Test Mode • OutOfRange for metering
S27-3	1, 2	data-update (dupd)				
S28	1, 2	GetURCBValues	TP		Y	
S29	1, 2	SetURCBValues	TP		Y	
Logging						
Log Control Block						
S30	1, 2	GetLCBValues	TP			
S31	1, 2	SetLCBValues	TP			
Log	1, 2					
S32	1, 2	QueryLogByTime	TP			
S33	1, 2	QueryLogByEntry	TP			
S34	1, 2	GetLogStatusValues	TP			
Generic Substation Event Model (GSE)						
GOOSE						
S35	1, 2	SendGOOSEMessage	MC	Y	Y	IED supports GOOSE publish & subscription
GOOSE-CONTROL-BLOCK						
S36	1, 2	GetReference	TP			
S37	1, 2	GetGOOSEElementNumber	TP			
S38	1, 2	GetGoCBValues	TP		Y	
S39	1, 2	SetGoCBValues	TP		Y	
GSSE						
S40	1	SendGSSEMessage	MC			Deprecated
GSSE-CONTROL-BLOCK						
S41	1	GetReference	TP			Deprecated

	Ed.	Services	AA: TP/MC	Client (C)	Server (S)	Comments
S42	1	GetGSSElementNumber	TP			Deprecated
S43	1	GetGscBValues	TP			Deprecated
S44	1	SetGscBValues	TP			Deprecated
Transmission of Sampled Value Model (SVC)						
Multicast SVC						
S45	1, 2	SendMSVMessage	MC			
Multicast Sample Value Control Block						
S46	1, 2	GetMSVCBValues	TP			
S47	1, 2	SetMSVCBValues	TP			
Unicast SVC						
S48	1, 2	SendUSVMessage	TP			
Unicast Sample Value Control Block						
S49	1, 2	GetUSVCBValues	TP			
S50	1, 2	SetUSVCBValues	TP			
Control						
S51	1, 2	Select			Y	SBO Normal Security
S52	1, 2	SelectWithValue	TP		Y	SBO Enhanced Security
S53	1, 2	Cancel	TP		Y	
S54	1, 2	Operate	TP		Y	
S55	1, 2	Command-Termination	TP		Y	
S56	1, 2	TimeActivated-Operate	TP			
File Transfer						
S57	1, 2	GetFile	TP		Y	
S58	1, 2	SetFile	TP			
S59	1, 2	DeleteFile	TP			
S60	1, 2	GetFileAttributeValue	TP		Y	
S61	1, 2	GetServerDirectory(FILE-SYSTEM)	TP		Y	
Time						
T1	1, 2	Time resolution of internal clock			2ms	Nearest negative power of 2 in seconds
T2	1, 2	Time accuracy of internal clock				T0
						T1
						T2
						T3
						T4
					Y	T5 (μ s) ($\leq 1 \mu$ s), T3 ≥ 20)
T3	1, 2	Supported TimeStamp resolution	-		1 μ s	Nearest negative power of 2 in seconds

Table 2: Service conformance statement

AA: Application association type

TP: Two part (for MMS)

MC: Multicast (for GOOSE and SMV)



Imagination at work

Grid Solutions
St Leonards Building
Redhill Business Park
Stafford, ST16 1WT, UK
+44 (0) 1785 250 070
www.gegridsolutions.com/contact

© 2024 General Electric. All rights reserved. Information contained in this document is indicative only.
No representation or warranty is given or should be relied on that it is complete or correct or will apply to any particular project.
This will depend on the technical and commercial circumstances. It is provided without liability and is subject to change without notice.
Reproduction, use or disclosure to third parties, without express written authority, is strictly prohibited.