

GE

Energy Connections

Model 563

Current Transformer
Window Size 4.00" x 5.38"

Application

Relaying and metering.

Frequency

50-400 Hz.

Insulation Level

600 Volts, 10 kV BIL full wave.

Insulation System

Temperature Class H (180°C.)

Continuous Thermal Current Rating Factor

1.33 at 30 °C. amb.,
 1.0 at 55 °C. amb.

Terminals are brass screws No. 10-32 with one flatwasher and lockwasher.

Approximate weight 12 lbs.





REGULATORY AGENCY APPROVALS
 E93779  LR89403
 Manufactured to meet the requirements of ANSI/IEEE C57.13.
 Classified by U.L. in accordance with IEC 44-1

Model 563

Catalog Number	Current Ratio	Relay Class	ANSI Metering Class at 60 Hz					Secondary Winding Resistance (Ω @ 75 °C)
			BO.1	BO.2	BO.5	BO.9	B1.8	
563-202	2,000:5	C50	0.3	0.3	0.3	0.3	0.3	0.995
563-252	2,500:5	C50	0.3	0.3	0.3	0.3	0.3	1.244
563-302	3,000:5	C20	0.3	0.3	0.3	0.3	0.3	1.382
563-322	3,200:5	C20	0.3	0.3	0.3	0.3	0.3	1.474
563-402	4,000:5	C20	0.3	0.3	0.3	0.3	0.3	1.842



Model 563



GEGridSolutions.com

Grid-AIS-L4-ITL_Model_563-1324-2017_05-EN. © Copyright 2017. General Electric Company and Instrument Transformers LLC reserve the right to change specifications of described products at any time without notice and without obligation to notify any person of such changes.

Worldwide Contact Center

Web: www.GEGridSolutions.com/contact

Phone: +44 (0) 1785 250 070

USA and Canada: +1 (0) 800 547 8629

Europe, Middle East and Africa: +34 (0) 94 485 88 00

