

# Model 592

## Current Transformer with Cast Resin Construction Window Size 5.00”x 14.00”

### Application

Relaying.

### Frequency

50-400 Hz.

### Insulation Level

600 Volts, 10 kV BIL full wave.

### Continuous Thermal Current Rating Factor

2.0 at 30 °C. amb.,  
1.5 at 55 °C. amb.

Terminals are brass screws No. 10-32  
with one flatwasher and lockwasher.

Approximate weight 150 lbs.



#### REGULATORY AGENCY APPROVALS



Manufactured to meet the requirements of ANSI/IEEE C57.13.  
Classified by U.L. in accordance with IEC 44-1

## Model 592

Catalog Number	Current Ratio	Relay Class	Secondary Winding Resistance (Ω @ 75 °C)
592-500	50:5	C15	0.014
592-101	100:5	C30	0.028
592-201	200:5	C60	0.056
592-301	300:5	C100	0.097
592-401	400:5	C120	0.123
592-501	500:5	C150	0.161
592-601	600:5	C200	0.193



