



GE VERNOVA

MiCOM P40 Agile

P841B

MICS

Model Implementation Conformance Statement - IEC 61850 Edition 2

Software Version: AB

Publication Reference: P841B-MC2-EN-AB-1.1



CONTENTS

1	Model Implementation Conformance Statement (MICS)	3
1.1	Introduction	3
1.2	Objective	3
1.3	Logical Device Definitions	3
1.4	Logical Node Definitions	10
1.5	Common Data Class Definitions	37
1.6	Common Data Attribute Type Definitions	59
1.7	Enumerated Type Definitions	62
1.8	MMS Data-Type Conversions	71

1 MODEL IMPLEMENTATION CONFORMANCE STATEMENT (MICS)

1.1 INTRODUCTION

This specification is the Model Implementation Conformance Statement (MICS) and presents the top-level IEC 61850 data model that has been implemented. The definitions of all used Logical Nodes and their associated Common Data Classes, components and associated enumerated values are also included for completeness.

The reader is expected to be conversant with the terminology presented within the IEC 61850 part 7 series of specifications.

1.2 OBJECTIVE

To provide comprehensive details of the standard data object model elements supported by the device. The MICS is conformant to the devices associated ICD (Substation Configuration Language) file, according to part 6 of the IEC 61850 standards. The layout of the presented tables within this document are conformant to the part 7 series of the IEC 61850 standard specifications with the following exceptions:

- The "Trigger Options" field is not presented
- The "M/O" field is not present as the definitions are as deployed within the model
- An additional column "X" is used to signify GE custom attributes

1.3 LOGICAL DEVICE DEFINITIONS

The MiCOM relay implements an IEC 61850 server that can contain one or more Logical Devices. Each Logical Device contains a data model built from instances of specific Logical Nodes and must consist of at least an instance of the LPHD Logical Node (which is responsible for providing physical device information) and an instance of the LLN0 Logical Node (for addressing common issues across the Logical Device).

The IEC 61850 data model is contained within the Logical Devices detailed in the table below. All MiCOM devices will name the supported Logical Devices consistently to ensure that data model variables with the same purpose will have the same name within each MiCOM server.

Logical Device	Comment/Usage
AutoControl	Command and controls used for Automatic Control
AutoRec1	Auto Reclose Control Domain for CB 1
AutoRec2	Auto Reclose Control Domain for CB 2
AutoSynChk1	Automatically Synchronism Check Control Domain for CB 1
AutoSynChk2	Automatically Synchronism Check Control Domain for CB 2
CBControl	Commands and controls for CB
CtlCB1	Control CB 1
CtlCB1Fail	CBFail Control Domain for CB 1
CtlCB2	Control CB 2
CtlCB2Fail	CBFail Control Domain for CB 2
CtlSw	Switch Control
Measurements	Measurements Domain
PloCnt	Programmable Logic Counters
Protection	Protection Domain
ProtEfd	Derived Earth Fault Protection Domain
ProtEft	Transient Ground Fault Detection
ProtFrq	Frequency Protection
ProtNegSeq	Negative Sequence Protection Domain
ProtNvd	Residual Voltage Protection Domain

Logical Device	Comment/Usage
ProtOvCur	Overcurrent Control Domain
ProtOvThm	Over Thermal Protection Domain
ProtPwr	Directional Power Protection Domain
ProtRteChgFrq	Frequency Change Ratio Protection Domain
ProtSenEF	LD for Sensitive Earth Fault Protection
ProtVtp	Time-voltage Protection Domain
Records	Records Domain
System	System Domain

1.3.1 IEC 61850 LOGICAL DEVICE DATA MODEL

The IEC 61850 Logical Device top-level data model consists of instances of Logical Nodes. The data model name for a Logical Node instance is constructed from an optional prefix (known as the wrapper), the Logical Node name, and an instance ID (or suffix).

The presented data model is in an alphabetically sorted order, rather than a logical order, because this is the natural order of the data when presented by a native MMS browser. (Higher level browsers can of course impart any ordering that they desire).

LD	LN Instance	LN Type	Description
AutoControl	LLN0	LLN0_STANDARD	Auto Control Logical Device
	LPHD1	LPHD_STANDARD	Px40 Physical Device Information
AutoRec1	ArcPTRC16	PTRC_INDIVID_NO_SEG	Protection Trip for CB 1 Auto Reclose
	ArcRREC1	RREC_NO_SEG	Auto Reclose Control Domain for CB 1
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Auto Reclose Control in CB1
AutoRec2	ArcPTRC17	PTRC_INDIVID_NO_SEG	Protection Trip for CB 2 Auto Reclose
	ArcRREC2	RREC_NO_SEG	Auto Reclose Control Domain for CB 2
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Auto Reclose Control in CB2
AutoSynChk1	AscRSYN1	RSYN_DIFCLC_ENH	System Checks (CB 1) - Check Sync 1
	AscRSYN2	RSYN_DIFCLC_ENH	System Checks (CB 1) - Check Sync 2
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for CB1 Automatic Synchronism Check Control
AutoSynChk2	AscRSYN3	RSYN_DIFCLC_ENH	System Checks (CB 2) - Check Sync 1
	AscRSYN4	RSYN_DIFCLC_ENH	System Checks (CB 2) - Check Sync 2
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for CB2 Automatic Synchronism Check Control
CBControl	LLN0	LLN0_STANDARD	CB Control Logical Device
	LPHD1	LPHD_STANDARD	Px40 Physical Device Information
CtlCB1	CB1CILO1	CILO_INTERLOCK	Circuit Breaker Interlocking for CB1
	CB1CSWI1	CSWI_PRIV	Switch Controller for CB1
	CB1PTRC1	PTRC_GLOBAL	Protection trip for CB 1 Control
	CB1XCBR1	XCBR_BASIC	Circuit Breaker 1 Monitoring (Pole 1)
	CB1XCBR2	XCBR_BASIC	Circuit Breaker 1 Monitoring (Pole 2)
	CB1XCBR3	XCBR_BASIC	Circuit Breaker 1 Monitoring (Pole 3)
	CB1XCBR4	XCBR_BASIC	Circuit Breaker 1 Monitoring for 3-pole
	LLN0	LLN0_STANDARD	Logical Device for CB 1 Control

LD	LN Instance	LN Type	Description
CtiCB1Fail			
	Cb1fPTRC18	PTRC_INDIVID_NO_SEG	Protection trip for CB1 Fail
	CbfRBRF1	RBRF_EXTTRIP	CB1 Fail 1
	CbfRBRF2	RBRF_EXTTRIP	CB1 Fail 2
	LLN0	LLN0_STANDARD_CBFAIL	Logical Device for CB1 Fail Control
CtiCB2			
	CB2CILO1	CILO_INTERLOCK	Circuit Breaker Interlocking for CB2
	CB2CSWI1	CSWI_PRIV	
	CB2PTRC2	PTRC_GLOBAL	Protection trip for CB 2 Control
	CB2XCBR1	XCBR_BASIC	Circuit Breaker 2 Monitoring (Pole 1)
	CB2XCBR2	XCBR_BASIC	Circuit Breaker 2 Monitoring (Pole 2)
	CB2XCBR3	XCBR_BASIC	Circuit Breaker 2 Monitoring (Pole 3)
	CB2XCBR4	XCBR_BASIC	Circuit Breaker 2 Monitoring for 3-pole
	LLN0	LLN0_STANDARD	Logical Device for CB 2 Control
CtiCB2Fail			
	Cb2fPTRC19	PTRC_INDIVID_NO_SEG	Protection trip for CB2 Fail
	CbfRBRF3	RBRF_EXTTRIP	CB2 Fail 1
	CbfRBRF4	RBRF_EXTTRIP	CB2 Fail 2
	LLN0	LLN0_STANDARD_CBFAIL	Logical Device for CB1 Fail Control
CtiSw			
	LLN0	LLN0_STANDARD	Switch Control Logical Device
	SwCILO1	CILO_INTERLOCK	XSWI1 Interlocking
	SwCILO2	CILO_INTERLOCK	XSWI2 Interlocking
	SwCILO3	CILO_INTERLOCK	XSWI3 Interlocking
	SwCILO4	CILO_INTERLOCK	XSWI4 Interlocking
	SwCILO5	CILO_INTERLOCK	XSWI5 Interlocking
	SwCILO6	CILO_INTERLOCK	XSWI6 Interlocking
	SwCILO7	CILO_INTERLOCK	XSWI7 Interlocking
	SwCILO8	CILO_INTERLOCK	XSWI8 Interlocking
	SwCSWI1	CSWI_PRIV	Control Sw 1
	SwCSWI2	CSWI_PRIV	Control Sw 2
	SwCSWI3	CSWI_PRIV	Control Sw 3
	SwCSWI4	CSWI_PRIV	Control Sw 4
	SwCSWI5	CSWI_PRIV	Control Sw 5
	SwCSWI6	CSWI_PRIV	Control Sw 6
	SwCSWI7	CSWI_PRIV	Control Sw 7
	SwCSWI8	CSWI_PRIV	Control Sw 8
	SwXSWI1	XSWI_BASIC	Switch Monitoring and Control
	SwXSWI2	XSWI_BASIC	Switch Monitoring and Control
	SwXSWI3	XSWI_BASIC	Switch Monitoring and Control
	SwXSWI4	XSWI_BASIC	Switch Monitoring and Control
	SwXSWI5	XSWI_BASIC	Switch Monitoring and Control
	SwXSWI6	XSWI_BASIC	Switch Monitoring and Control
	SwXSWI7	XSWI_BASIC	Switch Monitoring and Control
	SwXSWI8	XSWI_BASIC	Switch Monitoring and Control
Measurements			
	LLN0	LLN0_STANDARD_MEA	Measurements Logical Device
	LPHD1	LPHD_STANDARD	Physical Device Information
	PriAvgMMXU1	MMXU_METER_AV	Primary Average Value of Fixed Measurements
	PriAvgMMXU2	MMXU_METER_AV	Primary Average Value of Rolled Measurements

LD	LN Instance	LN Type	Description
	PriFitMLFR1	MLFR_FAULT_RECORD_NODIF_CB2	Measurements during the Latest Fault Record without Differential Protection for two CBs
	PriFouMMXU1	MMXU_FOURIER_CB2_EXT	Primary Fourier Measurements including Df/Dt
	PriMaxMMXU1	MMXU_METER_MAX	Primary Maximum Value of Measurement
	PriMMTR1	MMTR_PRIV	Primary based metering quantities
	PriMSQI1	MSQI_ALL	Primary Sequence Measurements
	PriPreFitMLFR1	MLFR_PRE_FAULT	Fault Record before fault
	PriRmsMMXU1	MMXU_RMS	Primary RMS Measurements
	PriVcpMSQI1	MSQI_VOLTAGE	Primary Compensated Overvoltage Measurements
	SecAvgMMXU1	MMXU_METER_AV	Secondary Average Value of Fixed Measurements
	SecAvgMMXU2	MMXU_METER_AV	Secondary Average Value of Rolled Measurements
	SecFouMMXU1	MMXU_FOURIER_CB2_EXT	Secondary Fourier Measurements including Df/Dt
	SecMaxMMXU1	MMXU_METER_MAX	Secondary Maximum Value of Measurement
	SecMMTR1	MMTR_PRIV	Secondary based metering quantities
	SecMSQI1	MSQI_ALL	Secondary Sequence Measurements
	SecRmsMMXU1	MMXU_RMS	Secondary RMS Measurements
	SecVcpMSQI1	MSQI_VOLTAGE	Secondary Compensated Overvoltage Measurements
PloCnt			
	CntFCNT1	FCNT_COUNTER	PSL Settable Counter 1
	CntFCNT10	FCNT_COUNTER	PSL Settable Counter 10
	CntFCNT11	FCNT_COUNTER	PSL Settable Counter 11
	CntFCNT12	FCNT_COUNTER	PSL Settable Counter 12
	CntFCNT13	FCNT_COUNTER	PSL Settable Counter 13
	CntFCNT14	FCNT_COUNTER	PSL Settable Counter 14
	CntFCNT15	FCNT_COUNTER	PSL Settable Counter 15
	CntFCNT16	FCNT_COUNTER	PSL Settable Counter 16
	CntFCNT17	FCNT_COUNTER	PSL Settable Counter 17
	CntFCNT18	FCNT_COUNTER	PSL Settable Counter 18
	CntFCNT19	FCNT_COUNTER	PSL Settable Counter 19
	CntFCNT2	FCNT_COUNTER	PSL Settable Counter 2
	CntFCNT20	FCNT_COUNTER	PSL Settable Counter 20
	CntFCNT21	FCNT_COUNTER	PSL Settable Counter 21
	CntFCNT22	FCNT_COUNTER	PSL Settable Counter 22
	CntFCNT23	FCNT_COUNTER	PSL Settable Counter 23
	CntFCNT24	FCNT_COUNTER	PSL Settable Counter 24
	CntFCNT25	FCNT_COUNTER	PSL Settable Counter 25
	CntFCNT26	FCNT_COUNTER	PSL Settable Counter 26
	CntFCNT27	FCNT_COUNTER	PSL Settable Counter 27
	CntFCNT28	FCNT_COUNTER	PSL Settable Counter 28
	CntFCNT29	FCNT_COUNTER	PSL Settable Counter 29
	CntFCNT3	FCNT_COUNTER	PSL Settable Counter 3
	CntFCNT30	FCNT_COUNTER	PSL Settable Counter 30
	CntFCNT31	FCNT_COUNTER	PSL Settable Counter 31
	CntFCNT32	FCNT_COUNTER	PSL Settable Counter 32
	CntFCNT4	FCNT_COUNTER	PSL Settable Counter 4
	CntFCNT5	FCNT_COUNTER	PSL Settable Counter 5
	CntFCNT6	FCNT_COUNTER	PSL Settable Counter 6
	CntFCNT7	FCNT_COUNTER	PSL Settable Counter 7
	CntFCNT8	FCNT_COUNTER	PSL Settable Counter 8
	CntFCNT9	FCNT_COUNTER	PSL Settable Counter 9
	LLN0	LLN0_STANDARD	Programmable Logic Counters Logical Device

LD	LN Instance	LN Type	Description
Protection			
	LLN0	LLN0_STANDARD	Protection Logical Device with Standard Template
	LPHD1	LPHD_STANDARD	Physical Device Information
ProtEfd			
	EfdPTOC1	PTOC_NEU	IN1> 1 Earth Fault (Derived)
	EfdPTOC2	PTOC_NEU	IN1> 2 Earth Fault (Derived)
	EfdPTOC3	PTOC_NEU	IN1> 3 Earth Fault (Derived)
	EfdPTOC4	PTOC_NEU	IN1> 4 Earth Fault (Derived)
	EfdPTRC9	PTRC_INDIVID_NO_SEG	Protection trip for Earth Fault (Derived) protection
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Efd Protection
ProtEft			
	EftPTEF1	PTEF_NEU	Transient Earth Fault Alarm
	EftPTRC21	PTRC_INDIVID_NO_SEG	Transient Earth Fault Alarm
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Node for Eft Protection
ProtFrq			
	FrqPTOF1	PTOF_NO_SEG	F> 1 Overfrequency
	FrqPTOF2	PTOF_NO_SEG	F> 2 Overfrequency
	FrqPTRC10	PTRC_INDIVID_NO_SEG	Protection trip for Frequency Protection
	FrqPTUF1	PTUF_NO_SEG	F< 1 Underfrequency
	FrqPTUF2	PTUF_NO_SEG	F< 2 Underfrequency
	FrqPTUF3	PTUF_NO_SEG	F< 3 Underfrequency
	FrqPTUF4	PTUF_NO_SEG	F< 4 Underfrequency
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Frequency Protection
ProtNegSeq			
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Negative Sequence Protection
	NgcPTOC1	PTOC_NO_SEG	I2> 1 Negative Sequence
	NgcPTOC2	PTOC_NO_SEG	I2> 2 Negative Sequence
	NgcPTOC3	PTOC_NO_SEG	I2> 3 Negative Sequence
	NgcPTOC4	PTOC_NO_SEG	I2> 4 Negative Sequence
	NgcPTRC11	PTRC_INDIVID_NO_SEG	Protection trip for Negative Sequence Protection
ProtNvd			
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Nvd Protection
	VtpResPTOV1	PTOV_NEU	VN> 1 Residual Overvoltage
	VtpResPTOV2	PTOV_NEU	VN> 2 Residual Overvoltage
	VtpResPTRC14	PTRC_INDIVID_NO_SEG	Protection trip for Nvd protection
ProtOvCur			
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Overcurrent Protection
	OcpPTOC1	PTOC_SEG	I> 1 Overcurrent
	OcpPTOC2	PTOC_SEG	I> 2 Overcurrent
	OcpPTOC3	PTOC_SEG	I> 3 Overcurrent
	OcpPTOC4	PTOC_SEG	I> 4 Overcurrent
	OcpPTRC7	PTRC_INDIVID_NO_SEG	Protection trip for Overcurrent Protection
ProtOvThm			
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Thermal Overload Protection
	ThmPTRC20	PTRC_INDIVID_NO_SEG	Protection trip for thermal Overload
	ThmPTTR1	PTTR_NO_SEG	Thermal Overload
ProtPwr			
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logic device for directional power protection
	PdpPDOP1	PDOP_BASIC	Directional overpower stage 1
	PdpPDOP2	PDOP_BASIC	Directional overpower stage 2
	PdpPDOP3	PDOP_BASIC	Directional overpower stage 3

LD	LN Instance	LN Type	Description
	PdpPDOP4	PDOP_BASIC	Directional overpower stage 4
	PdpPDUP1	PDUP_BASIC	Directional underpower stage 1
	PdpPDUP2	PDUP_BASIC	Directional underpower stage 2
	PdpPDUP3	PDUP_BASIC	Directional underpower stage 3
	PdpPDUP4	PDUP_BASIC	Directional underpower stage 4
	PdpPTRC22	PTRC_INDIVID_NO_SEG	Protection trip for directional power
ProtRteChgFrq			
	DfpPFRC1	PFRC_NO_SEG	df/dt> 1 Frequency Rate of Change
	DfpPFRC2	PFRC_NO_SEG	df/dt> 2 Frequency Rate of Change
	DfpPFRC3	PFRC_NO_SEG	df/dt> 3 Frequency Rate of Change
	DfpPFRC4	PFRC_NO_SEG	df/dt> 4 Frequency Rate of Change
	DfpPTRC8	PTRC_INDIVID_NO_SEG	Protection trip for Frequency Rate Change Protection
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Frequency Rate Change Protection
ProtSenEF			
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical device for Sensitive Earth Fault protection
	SenEftPSDE1	PSDE_NEU	ISEF>1 Sensitive Earth fault
	SenEftPSDE2	PSDE_NEU	ISEF>2 Sensitive Earth fault
	SenEftPSDE3	PSDE_NEU	ISEF>3 Sensitive Earth fault
	SenEftPSDE4	PSDE_NEU	ISEF>4 Sensitive Earth fault
	SenEftPTRC13	PTRC_INDIVID_NO_SEG	Protection trip for Sensitive Earth Fault
	SenRefPDIF1	PDIF_NEU	IREF> 1 Restricted Earth Fault
ProtVtp			
	LLN0	LLN0_STANDARD_WITH_CTRLMOD	Logical Device for Vtp Protection
	VtpCmpPTOV1	PTOV_NO_SEG	Compensated V1> 1 Overvoltage
	VtpCmpPTOV2	PTOV_NO_SEG	Compensated V1> 2 Overvoltage
	VtpPhsPTOV1	PTOV_SEG	V> 1 Overvoltage
	VtpPhsPTOV2	PTOV_SEG	V> 2 Overvoltage
	VtpPhsPTRC12	PTRC_INDIVID_NO_SEG	Protection trip for Vtp Protection
	VtpPhsPTUV1	PTUV_SEG	V< 1 Undervoltage
	VtpPhsPTUV2	PTUV_SEG	V< 2 Undervoltage
Records			
	LLN0	LLN0_STANDARD	Records Logical Device
	LPHD1	LPHD_STANDARD	Physical Device Information
	RDRE1	RDRE_BASIC	Disturbance Recorder
	RFLO1	RFLO_BASIC	Fault Locator
System			
	AlmCALH1	CALH_ALARM	CALH_Alarm
	AlmCALH2	CALH_ALARM	CALH_Alarm
	AlmCALH3	CALH_ALARM	CALH_Alarm
	AlmCALH4	CALH_ALARM	CALH_Alarm
	AlmCALH5	CALH_ALARM	CALH_Alarm
	AlmCALH6	CALH_ALARM	CALH_Alarm
	AlmCALH7	CALH_ALARM	CALH_Alarm
	AlmCALH8	CALH_ALARM	CALH_Alarm
	AlmGGIO1	GGIO_ALM_128	Alarms
	FnkGGIO1	GGIO_IND_10	Function Keys
	GosGGIO1	GGIO_IND_128	GOOSE Input Signals
	GosGGIO2	GGIO_IND_128	GOOSE Output Signals
	LedGGIO1	GGIO_IND_23	Red LED Signals
	LedGGIO2	GGIO_IND_23	Green LED Signals
	LGOS1	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 1

LD	LN Instance	LN Type	Description
	LGOS57	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 57
	LGOS58	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 58
	LGOS59	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 59
	LGOS6	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 6
	LGOS60	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 60
	LGOS61	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 61
	LGOS62	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 62
	LGOS63	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 63
	LGOS64	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 64
	LGOS7	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 7
	LGOS8	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 8
	LGOS9	LGOS_SYSTEM	Monitoring of GOOSE Messages for External Publisher 9
	LLN0	LLN0_SYSTEM	System Logical Device
	LPHD1	LPHD_SYSTEM	Physical Device Information for System Logical Device
	LSVS1	LSVS_SYSTEM	Sampled Value Subscription for SV LN1
	LSVS2	LSVS_SYSTEM	Sampled Value Subscription for SV LN2
	LSVS3	LSVS_SYSTEM	Sampled Value Subscription for SV LN3
	LSVS4	LSVS_SYSTEM	Sampled Value Subscription for SV LN4
	LSVS5	LSVS_SYSTEM	Sampled Value Subscription for SV LN5
	LSVS6	LSVS_SYSTEM	Sampled Value Subscription for SV LN6
	LSVS7	LSVS_SYSTEM	Sampled Value Subscription for SV LN7
	LSVS8	LSVS_SYSTEM	Sampled Value Subscription for SV LN8
	LSVS9	LSVS_SYSTEM	Sampled Value Subscription for SV LN9
	LTIM1	LTIM_SYSTEM	Time Management
	LTMS1	LTMS_SYSTEM	Time master supervision
	NP1LCCH1	LCCH_SYSTEM_ENG_PORT	Physical communication channel supervision
	NP2LCCH2	LCCH_SYSTEM	Physical communication channel supervision
	OptGGIO1	GGIO_IND_40	Opto (40) Inputs
	PloGGIO1	GGIO_IND_32_CTRL	Controllable Inputs
	RlyGGIO1	GGIO_IND_43	Output (43) Contacts
	TVTR1	TVTR_SYSTEM	Voltage transformer monitor
	UsrAlmGGIO1	GGIO_USER_ALM_32	User Alarms
	UsrGGIO1	GGIO_IND_DPS_8	User Mapped (PSL) Double Point Status Indications

1.4 LOGICAL NODE DEFINITIONS

The definition tables for each of the Logical Nodes in the top-level data model are presented in the following sub-sections.

The following table presents a summary of the Logical Node templates used across the Logical Devices within the overall IEC 61850 product data model:

LN Type	(LN Class)	Description	Name Space
CALH_ALARM	(CALH)	Logical Node for Group Alarms, Group Warnings and Group Indications	IEC 61850-7-4:2007B
CILO_INTERLOCK	(CILO)	Control Interlocking	IEC 61850-7-4:2007B
CSWI_PRIV	(CSWI)	Switch controller (with extended DO 'CtlEna')	IEC 61850-7-4:2007B
FCNT_COUNTER	(FCNT)	Counter	IEC 61850-7-4:2007B
GGIO_ALM_128	(GGIO)	Generic process I/O (w.r.t 128 Alarm Elements)	IEC 61850-7-4:2007B
GGIO_IND_10	(GGIO)	Generic Process I/O (w.r.t 10 Indication Elements)	IEC 61850-7-4:2007B
GGIO_IND_128	(GGIO)	Generic process I/O (w.r.t 128 indications)	IEC 61850-7-4:2007B
GGIO_IND_23	(GGIO)	Generic process I/O (w.r.t 23 Indication Elements)	IEC 61850-7-4:2007B

LN Type	(LN Class)	Description	Name Space
GGIO_IND_32_CTRL	(GGIO)	Generic process I/O (w.r.t 32 Indications Ctrl i/p)	IEC 61850-7-4:2007B
GGIO_IND_40	(GGIO)	Generic process I/O (w.r.t 40 Indication Elements)	IEC 61850-7-4:2007B
GGIO_IND_43	(GGIO)	Generic process I/O (w.r.t 43 Indication Elements)	IEC 61850-7-4:2007B
GGIO_IND_DPS_8	(GGIO)	Generic process I/O (w.r.t 8 Dual Point Status Indication Elements)	IEC 61850-7-4:2007B
GGIO_USER_ALM_32	(GGIO)	Generic process I/O	IEC 61850-7-4:2007B
LCCH_SYSTEM_ENG_PORT	(LCCH)	Physical communication channel supervision	IEC 61850-7-4:2007B
LCCH_SYSTEM	(LCCH)	Physical communication channel supervision	IEC 61850-7-4:2007B
LGOS_SYSTEM	(LGOS)	Monitoring of GOOSE messages	IEC 61850-7-4:2007B
LLNO_STANDARD_CBFAIL	(LLNO)	Logical Node 0 in CB Fail	IEC 61850-7-4:2007B
LLNO_STANDARD_MEA	(LLNO)	Measurements Logical Node 0	IEC 61850-7-4:2007B
LLNO_STANDARD_WITH_CTRLMOD	(LLNO)	Logical Node 0	IEC 61850-7-4:2007B
LLNO_SYSTEM	(LLNO)	System Logical Node 0	IEC 61850-7-4:2007B
LLNO_STANDARD	(LLNO)	General Logical Node 0	IEC 61850-7-4:2007B
LPHD_STANDARD	(LPHD)	Px40 Physical Device Information	IEC 61850-7-4:2007B
LPHD_SYSTEM	(LPHD)	Px40 Physical Device Information (used for Logical Device System only)	IEC 61850-7-4:2007B
LSVS_SYSTEM	(LSVS)	Sampled value subscription	IEC 61850-7-4:2007B
LTIM_SYSTEM	(LTIM)	Time management	IEC 61850-7-4:2007B
LTMS_SYSTEM	(LTMS)	Time master supervision	IEC 61850-7-4:2007B
MLFR_FAULT_RECORD_NODIF_CB2	(MLFR)	Measurements of Fault Record without Differential Protection	GE-SII:Px40:2013A
MLFR_PRE_FAULT	(MLFR)	Measurements of Fault Record	GE-SII:Px40:2013A
MMTR_PRIV	(MMTR)	Metering	IEC 61850-7-4:2007B
MMXU_METER_MAX	(MMXU)	Standard measurements (w.r.t Current, Real + Reactive Power - Max values)	IEC 61850-7-4:2007B
MMXU_METER_AV	(MMXU)	Metering Statistics (w.r.t Current, Real + Reactive Power - Average values)	IEC 61850-7-4:2007B
MMXU_RMS	(MMXU)	Standard Measurements (w.r.t RMS Values)	IEC 61850-7-4:2007B
MMXU_FOURIER_CB2_EXT	(MMXU)	Standard measurements for CB2 (w.r.t Fourier Values Including Df/Dt)	IEC 61850-7-4:2007B
MSQI_ALL	(MSQI)	Sequence and imbalance (w.r.t Pos, Neg, Zero)	IEC 61850-7-4:2007B
MSQI_VOLTAGE	(MSQI)	Sequence and imbalance (w.r.t Pos, Neg, Zero Voltage Only)	IEC 61850-7-4:2007B
PDIF_NEU	(PDIF)	Differential (w.r.t Neutral)	IEC 61850-7-4:2007B
PDOP_BASIC	(PDOP)	Directional overpower	IEC 61850-7-4:2007B
PDUP_BASIC	(PDUP)	Directional underpower	IEC 61850-7-4:2007B
PFRC_NO_SEG	(PFRC)	Rate of change of frequency (w.r.t No Phase Segregation)	IEC 61850-7-4:2007B
PSDE_NEU	(PSDE)	Sensitive directional earthfault	IEC 61850-7-4:2007B
PTEF_NEU	(PTEF)	Transient earth fault (w.r.t Neutral)	IEC 61850-7-4:2007B
PTOC_NEU	(PTOC)	Timed Overcurrent (w.r.t Neutral)	IEC 61850-7-4:2007B
PTOC_NO_SEG	(PTOC)	Timed Overcurrent (w.r.t No Phase Segregation)	IEC 61850-7-4:2007B
PTOC_SEG	(PTOC)	Timed Overcurrent (w.r.t Phase Segregation)	IEC 61850-7-4:2007B
PTOF_NO_SEG	(PTOF)	Overfrequency (w.r.t No Phase Segregation)	IEC 61850-7-4:2007B
PTOV_SEG	(PTOV)	Overvoltage (w.r.t Phase Segregation)	IEC 61850-7-4:2007B
PTOV_NEU	(PTOV)	Overvoltage (w.r.t Neutral)	IEC 61850-7-4:2007B
PTOV_NO_SEG	(PTOV)	Overvoltage (w.r.t No Phase Segregation)	IEC 61850-7-4:2007B
PTRC_GLOBAL	(PTRC)	Protection trip for global protection conditioning	IEC 61850-7-4:2007B
PTRC_INDIVID_NO_SEG	(PTRC)	Protection trip for individual protection conditioning	IEC 61850-7-4:2007B
PTTR_NO_SEG	(PTTR)	Thermal overload (w.r.t No Phase Segregation)	IEC 61850-7-4:2007B
PTUF_NO_SEG	(PTUF)	Underfrequency (w.r.t No Phase Segregation)	IEC 61850-7-4:2007B
PTUV_SEG	(PTUV)	Undervoltage (w.r.t Phase Segregation)	IEC 61850-7-4:2007B
RBRF_EXTTRIP	(RBRF)	Breaker Failure (w.r.t External Tripping)	IEC 61850-7-4:2007B

LN Type	(LN Class)	Description	Name Space
RDRE_BASIC	(RDRE)	Disturbance Recorder function (w.r.t Mandatory Attributes only)	IEC 61850-7-4:2007B
RFLO_BASIC	(RFLO)	Fault Locator (w.r.t Mandatory Attributes only)	IEC 61850-7-4:2007B
RREC_NO_SEG	(RREC)	Autoreclosing (w.r.t No Phase Segregation)	IEC 61850-7-4:2007B
RSYN_DIFCLC_ENH	(RSYN)	Synchronism-check/Synchronising (w.r.t Calculated Differential Measurements)	IEC 61850-7-4:2007B
TVTR_SYSTEM	(TVTR)	Voltage transformer	IEC 61850-7-4:2007B
XCBR_BASIC	(XCBR)	Circuit Breaker (w.r.t Mandatory Attributes Only)	IEC 61850-7-4:2007B
XSWI_BASIC	(XSWI)	Circuit Switch (w.r.t Switch Status and Control)	IEC 61850-7-4:2007B

1.4.1 LOGICAL NODE: CALH_ALARM

Description: Logical Node for Group Alarms, Group Warnings and Group Indications

LN Class: CALH

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
GrAlm	SPS_WD	If true, a new group alarm trigger status has been activated by one of individual alarm trigger states.		
GrInd	SPS_WD	If true, a new group indication has been activated by one of individual indications		
GrWrn	SPS_WD	If true, a new group warning trigger status has been activated by one of individual warning trigger states		

1.4.2 LOGICAL NODE: CILO_INTERLOCK

Description: Control Interlocking

LN Class: CILO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
EnaOpn	SPS_WD	Enable OPEN Commands		
EnaCls	SPS_WD	Enable CLOSE Commands		

1.4.3 LOGICAL NODE: CSWI_PRIV

Description: Switch Controller (with Extended DO 'CtlEna')

LN Class: CSWI

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Loc	SPS_WD	Local control behaviour		
OpOpn	ACT_NO_SEG	Operation "open switch"	T	
OpCls	ACT_NO_SEG	Operation "close switch"	T	
OpCntRs	INC_MOD_STD	Resettable operation counter		
Pos	DPC_CTRL	Switch, general		
CtlEna	SPS_WD_PRIV	Control By		X

1.4.4 LOGICAL NODE: FCNT_COUNTER

Description: Counter

LN Class: FCNT

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
CntVal	BCR_PRIV	Counter		
RsCnt	SPC_CTRL_PRIV	Counter Reset		X

1.4.5 LOGICAL NODE: GGIO_ALM_128

Description: Generic Process I/O (w.r.t 128 Alarm Elements)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Alm1	SPS_D	General single alarm		
Alm2	SPS_D	General single alarm		
Alm3	SPS_D	General single alarm		
Alm4	SPS_D	General single alarm		
Alm5	SPS_D	General single alarm		
Alm6	SPS_D	General single alarm		
Alm7	SPS_D	General single alarm		
Alm8	SPS_D	General single alarm		
Alm9	SPS_D	General single alarm		
Alm10	SPS_D	General single alarm		
Alm11	SPS_D	General single alarm		
Alm12	SPS_D	General single alarm		
Alm13	SPS_D	General single alarm		
Alm14	SPS_D	General single alarm		
Alm15	SPS_D	General single alarm		
Alm16	SPS_D	General single alarm		
Alm17	SPS_D	General single alarm		
Alm18	SPS_D	General single alarm		
Alm19	SPS_D	General single alarm		
Alm20	SPS_D	General single alarm		
Alm21	SPS_D	General single alarm		
Alm22	SPS_D	General single alarm		
Alm23	SPS_D	General single alarm		
Alm24	SPS_D	General single alarm		
Alm25	SPS_D	General single alarm		
Alm26	SPS_D	General single alarm		
Alm27	SPS_D	General single alarm		
Alm28	SPS_D	General single alarm		
Alm29	SPS_D	General single alarm		
Alm30	SPS_D	General single alarm		
Alm31	SPS_D	General single alarm		
Alm32	SPS_D	General single alarm		

Attribute	Attr. Type	Explanation	T	X
Alm33	SPS_D	General single alarm		
Alm34	SPS_D	General single alarm		
Alm35	SPS_D	General single alarm		
Alm36	SPS_D	General single alarm		
Alm37	SPS_D	General single alarm		
Alm38	SPS_D	General single alarm		
Alm39	SPS_D	General single alarm		
Alm40	SPS_D	General single alarm		
Alm41	SPS_D	General single alarm		
Alm42	SPS_D	General single alarm		
Alm43	SPS_D	General single alarm		
Alm44	SPS_D	General single alarm		
Alm45	SPS_D	General single alarm		
Alm46	SPS_D	General single alarm		
Alm47	SPS_D	General single alarm		
Alm48	SPS_D	General single alarm		
Alm49	SPS_D	General single alarm		
Alm50	SPS_D	General single alarm		
Alm51	SPS_D	General single alarm		
Alm52	SPS_D	General single alarm		
Alm53	SPS_D	General single alarm		
Alm54	SPS_D	General single alarm		
Alm55	SPS_D	General single alarm		
Alm56	SPS_D	General single alarm		
Alm57	SPS_D	General single alarm		
Alm58	SPS_D	General single alarm		
Alm59	SPS_D	General single alarm		
Alm60	SPS_D	General single alarm		
Alm61	SPS_D	General single alarm		
Alm62	SPS_D	General single alarm		
Alm63	SPS_D	General single alarm		
Alm64	SPS_D	General single alarm		
Alm65	SPS_D	General single alarm		
Alm66	SPS_D	General single alarm		
Alm67	SPS_D	General single alarm		
Alm68	SPS_D	General single alarm		
Alm69	SPS_D	General single alarm		
Alm70	SPS_D	General single alarm		
Alm71	SPS_D	General single alarm		
Alm72	SPS_D	General single alarm		
Alm73	SPS_D	General single alarm		
Alm74	SPS_D	General single alarm		
Alm75	SPS_D	General single alarm		
Alm76	SPS_D	General single alarm		
Alm77	SPS_D	General single alarm		
Alm78	SPS_D	General single alarm		
Alm79	SPS_D	General single alarm		
Alm80	SPS_D	General single alarm		
Alm81	SPS_D	General single alarm		
Alm82	SPS_D	General single alarm		
Alm83	SPS_D	General single alarm		

Attribute	Attr. Type	Explanation	T	X
Alm84	SPS_D	General single alarm		
Alm85	SPS_D	General single alarm		
Alm86	SPS_D	General single alarm		
Alm87	SPS_D	General single alarm		
Alm88	SPS_D	General single alarm		
Alm89	SPS_D	General single alarm		
Alm90	SPS_D	General single alarm		
Alm91	SPS_D	General single alarm		
Alm92	SPS_D	General single alarm		
Alm93	SPS_D	General single alarm		
Alm94	SPS_D	General single alarm		
Alm95	SPS_D	General single alarm		
Alm96	SPS_D	General single alarm		
Alm97	SPS_D	General single alarm		
Alm98	SPS_D	General single alarm		
Alm99	SPS_D	General single alarm		
Alm100	SPS_D	General single alarm		
Alm101	SPS_D	General single alarm		
Alm102	SPS_D	General single alarm		
Alm103	SPS_D	General single alarm		
Alm104	SPS_D	General single alarm		
Alm105	SPS_D	General single alarm		
Alm106	SPS_D	General single alarm		
Alm107	SPS_D	General single alarm		
Alm108	SPS_D	General single alarm		
Alm109	SPS_D	General single alarm		
Alm110	SPS_D	General single alarm		
Alm111	SPS_D	General single alarm		
Alm112	SPS_D	General single alarm		
Alm113	SPS_D	General single alarm		
Alm114	SPS_D	General single alarm		
Alm115	SPS_D	General single alarm		
Alm116	SPS_D	General single alarm		
Alm117	SPS_D	General single alarm		
Alm118	SPS_D	General single alarm		
Alm119	SPS_D	General single alarm		
Alm120	SPS_D	General single alarm		
Alm121	SPS_D	General single alarm		
Alm122	SPS_D	General single alarm		
Alm123	SPS_D	General single alarm		
Alm124	SPS_D	General single alarm		
Alm125	SPS_D	General single alarm		
Alm126	SPS_D	General single alarm		
Alm127	SPS_D	General single alarm		
Alm128	SPS_D	General single alarm		

1.4.6 LOGICAL NODE: GGIO_IND_10

Description: Generic Process I/O (w.r.t 10 Indication Elements)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Ind1	SPS_D	General Indication		
Ind2	SPS_D	General Indication		
Ind3	SPS_D	General Indication		
Ind4	SPS_D	General Indication		
Ind5	SPS_D	General Indication		
Ind6	SPS_D	General Indication		
Ind7	SPS_D	General Indication		
Ind8	SPS_D	General Indication		
Ind9	SPS_D	General Indication		
Ind10	SPS_D	General Indication		

1.4.7 LOGICAL NODE: GGIO_IND_128

Description: Generic Process I/O (w.r.t 128 indications)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Ind1	SPS_D	General Indication		
Ind2	SPS_D	General Indication		
Ind3	SPS_D	General Indication		
Ind4	SPS_D	General Indication		
Ind5	SPS_D	General Indication		
Ind6	SPS_D	General Indication		
Ind7	SPS_D	General Indication		
Ind8	SPS_D	General Indication		
Ind9	SPS_D	General Indication		
Ind10	SPS_D	General Indication		
Ind11	SPS_D	General Indication		
Ind12	SPS_D	General Indication		
Ind13	SPS_D	General Indication		
Ind14	SPS_D	General Indication		
Ind15	SPS_D	General Indication		
Ind16	SPS_D	General Indication		
Ind17	SPS_D	General Indication		
Ind18	SPS_D	General Indication		
Ind19	SPS_D	General Indication		
Ind20	SPS_D	General Indication		
Ind21	SPS_D	General Indication		
Ind22	SPS_D	General Indication		
Ind23	SPS_D	General Indication		
Ind24	SPS_D	General Indication		

Attribute	Attr. Type	Explanation	T	X
Ind25	SPS_D	General Indication		
Ind26	SPS_D	General Indication		
Ind27	SPS_D	General Indication		
Ind28	SPS_D	General Indication		
Ind29	SPS_D	General Indication		
Ind30	SPS_D	General Indication		
Ind31	SPS_D	General Indication		
Ind32	SPS_D	General Indication		
Ind33	SPS_D	General Indication		
Ind34	SPS_D	General Indication		
Ind35	SPS_D	General Indication		
Ind36	SPS_D	General Indication		
Ind37	SPS_D	General Indication		
Ind38	SPS_D	General Indication		
Ind39	SPS_D	General Indication		
Ind40	SPS_D	General Indication		
Ind41	SPS_D	General Indication		
Ind42	SPS_D	General Indication		
Ind43	SPS_D	General Indication		
Ind44	SPS_D	General Indication		
Ind45	SPS_D	General Indication		
Ind46	SPS_D	General Indication		
Ind47	SPS_D	General Indication		
Ind48	SPS_D	General Indication		
Ind49	SPS_D	General Indication		
Ind50	SPS_D	General Indication		
Ind51	SPS_D	General Indication		
Ind52	SPS_D	General Indication		
Ind53	SPS_D	General Indication		
Ind54	SPS_D	General Indication		
Ind55	SPS_D	General Indication		
Ind56	SPS_D	General Indication		
Ind57	SPS_D	General Indication		
Ind58	SPS_D	General Indication		
Ind59	SPS_D	General Indication		
Ind60	SPS_D	General Indication		
Ind61	SPS_D	General Indication		
Ind62	SPS_D	General Indication		
Ind63	SPS_D	General Indication		
Ind64	SPS_D	General Indication		
Ind65	SPS_D	General Indication		
Ind66	SPS_D	General Indication		
Ind67	SPS_D	General Indication		
Ind68	SPS_D	General Indication		
Ind69	SPS_D	General Indication		
Ind70	SPS_D	General Indication		
Ind71	SPS_D	General Indication		
Ind72	SPS_D	General Indication		
Ind73	SPS_D	General Indication		
Ind74	SPS_D	General Indication		
Ind75	SPS_D	General Indication		

Attribute	Attr. Type	Explanation	T	X
Ind76	SPS_D	General Indication		
Ind77	SPS_D	General Indication		
Ind78	SPS_D	General Indication		
Ind79	SPS_D	General Indication		
Ind80	SPS_D	General Indication		
Ind81	SPS_D	General Indication		
Ind82	SPS_D	General Indication		
Ind83	SPS_D	General Indication		
Ind84	SPS_D	General Indication		
Ind85	SPS_D	General Indication		
Ind86	SPS_D	General Indication		
Ind87	SPS_D	General Indication		
Ind88	SPS_D	General Indication		
Ind89	SPS_D	General Indication		
Ind90	SPS_D	General Indication		
Ind91	SPS_D	General Indication		
Ind92	SPS_D	General Indication		
Ind93	SPS_D	General Indication		
Ind94	SPS_D	General Indication		
Ind95	SPS_D	General Indication		
Ind96	SPS_D	General Indication		
Ind97	SPS_D	General Indication		
Ind98	SPS_D	General Indication		
Ind99	SPS_D	General Indication		
Ind100	SPS_D	General Indication		
Ind101	SPS_D	General Indication		
Ind102	SPS_D	General Indication		
Ind103	SPS_D	General Indication		
Ind104	SPS_D	General Indication		
Ind105	SPS_D	General Indication		
Ind106	SPS_D	General Indication		
Ind107	SPS_D	General Indication		
Ind108	SPS_D	General Indication		
Ind109	SPS_D	General Indication		
Ind110	SPS_D	General Indication		
Ind111	SPS_D	General Indication		
Ind112	SPS_D	General Indication		
Ind113	SPS_D	General Indication		
Ind114	SPS_D	General Indication		
Ind115	SPS_D	General Indication		
Ind116	SPS_D	General Indication		
Ind117	SPS_D	General Indication		
Ind118	SPS_D	General Indication		
Ind119	SPS_D	General Indication		
Ind120	SPS_D	General Indication		
Ind121	SPS_D	General Indication		
Ind122	SPS_D	General Indication		
Ind123	SPS_D	General Indication		
Ind124	SPS_D	General Indication		
Ind125	SPS_D	General Indication		
Ind126	SPS_D	General Indication		

Attribute	Attr. Type	Explanation	T	X
Ind127	SPS_D	General Indication		
Ind128	SPS_D	General Indication		

1.4.8 LOGICAL NODE: GGIO_IND_23

Description: Generic Process I/O (w.r.t 23 Indication Elements)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Ind1	SPS_D	General indication (binary input)		
Ind2	SPS_D	General indication (binary input)		
Ind3	SPS_D	General indication (binary input)		
Ind4	SPS_D	General indication (binary input)		
Ind5	SPS_D	General indication (binary input)		
Ind6	SPS_D	General indication (binary input)		
Ind7	SPS_D	General indication (binary input)		
Ind8	SPS_D	General indication (binary input)		
Ind9	SPS_D	General indication (binary input)		
Ind10	SPS_D	General indication (binary input)		
Ind11	SPS_D	General indication (binary input)		
Ind12	SPS_D	General indication (binary input)		
Ind13	SPS_D	General indication (binary input)		
Ind14	SPS_D	General indication (binary input)		
Ind15	SPS_D	General indication (binary input)		
Ind16	SPS_D	General indication (binary input)		
Ind17	SPS_D	General indication (binary input)		
Ind18	SPS_D	General indication (binary input)		
Ind19	SPS_D	General indication (binary input)		
Ind20	SPS_D	General indication (binary input)		
Ind21	SPS_D	General indication (binary input)		
Ind22	SPS_D	General indication (binary input)		
Ind23	SPS_D	General indication (binary input)		

1.4.9 LOGICAL NODE: GGIO_IND_32_CTRL

Description: Generic Process I/O (w.r.t 32 Indications Ctrl i/p)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
SPCS01	SPC_CONTROL	Single point controllable status output		
SPCS02	SPC_CONTROL	Single point controllable status output		
SPCS03	SPC_CONTROL	Single point controllable status output		
SPCS04	SPC_CONTROL	Single point controllable status output		
SPCS05	SPC_CONTROL	Single point controllable status output		
SPCS06	SPC_CONTROL	Single point controllable status output		
SPCS07	SPC_CONTROL	Single point controllable status output		

Attribute	Attr. Type	Explanation	T	X
SPCSO8	SPC_CONTROL	Single point controllable status output		
SPCSO9	SPC_CONTROL	Single point controllable status output		
SPCSO10	SPC_CONTROL	Single point controllable status output		
SPCSO11	SPC_CONTROL	Single point controllable status output		
SPCSO12	SPC_CONTROL	Single point controllable status output		
SPCSO13	SPC_CONTROL	Single point controllable status output		
SPCSO14	SPC_CONTROL	Single point controllable status output		
SPCSO15	SPC_CONTROL	Single point controllable status output		
SPCSO16	SPC_CONTROL	Single point controllable status output		
SPCSO17	SPC_CONTROL	Single point controllable status output		
SPCSO18	SPC_CONTROL	Single point controllable status output		
SPCSO19	SPC_CONTROL	Single point controllable status output		
SPCSO20	SPC_CONTROL	Single point controllable status output		
SPCSO21	SPC_CONTROL	Single point controllable status output		
SPCSO22	SPC_CONTROL	Single point controllable status output		
SPCSO23	SPC_CONTROL	Single point controllable status output		
SPCSO24	SPC_CONTROL	Single point controllable status output		
SPCSO25	SPC_CONTROL	Single point controllable status output		
SPCSO26	SPC_CONTROL	Single point controllable status output		
SPCSO27	SPC_CONTROL	Single point controllable status output		
SPCSO28	SPC_CONTROL	Single point controllable status output		
SPCSO29	SPC_CONTROL	Single point controllable status output		
SPCSO30	SPC_CONTROL	Single point controllable status output		
SPCSO31	SPC_CONTROL	Single point controllable status output		
SPCSO32	SPC_CONTROL	Single point controllable status output		

1.4.10 LOGICAL NODE: GGIO_IND_40

Description: Generic Process I/O (w.r.t 40 Indication Elements)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Ind1	SPS_D	General Indication		
Ind2	SPS_D	General Indication		
Ind3	SPS_D	General Indication		
Ind4	SPS_D	General Indication		
Ind5	SPS_D	General Indication		
Ind6	SPS_D	General Indication		
Ind7	SPS_D	General Indication		
Ind8	SPS_D	General Indication		
Ind9	SPS_D	General Indication		
Ind10	SPS_D	General Indication		
Ind11	SPS_D	General Indication		
Ind12	SPS_D	General Indication		
Ind13	SPS_D	General Indication		
Ind14	SPS_D	General Indication		
Ind15	SPS_D	General Indication		
Ind16	SPS_D	General Indication		

Attribute	Attr. Type	Explanation	T	X
Ind17	SPS_D	General Indication		
Ind18	SPS_D	General Indication		
Ind19	SPS_D	General Indication		
Ind20	SPS_D	General Indication		
Ind21	SPS_D	General Indication		
Ind22	SPS_D	General Indication		
Ind23	SPS_D	General Indication		
Ind24	SPS_D	General Indication		
Ind25	SPS_D	General Indication		
Ind26	SPS_D	General Indication		
Ind27	SPS_D	General Indication		
Ind28	SPS_D	General Indication		
Ind29	SPS_D	General Indication		
Ind30	SPS_D	General Indication		
Ind31	SPS_D	General Indication		
Ind32	SPS_D	General Indication		
Ind33	SPS_D	General Indication		
Ind34	SPS_D	General Indication		
Ind35	SPS_D	General Indication		
Ind36	SPS_D	General Indication		
Ind37	SPS_D	General Indication		
Ind38	SPS_D	General Indication		
Ind39	SPS_D	General Indication		
Ind40	SPS_D	General Indication		

1.4.11 LOGICAL NODE: GGIO_IND_43

Description: Generic Process I/O (w.r.t 43 Indication Elements)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Ind1	SPS_D	General Indication		
Ind2	SPS_D	General Indication		
Ind3	SPS_D	General Indication		
Ind4	SPS_D	General Indication		
Ind5	SPS_D	General Indication		
Ind6	SPS_D	General Indication		
Ind7	SPS_D	General Indication		
Ind8	SPS_D	General Indication		
Ind9	SPS_D	General Indication		
Ind10	SPS_D	General Indication		
Ind11	SPS_D	General Indication		
Ind12	SPS_D	General Indication		
Ind13	SPS_D	General Indication		
Ind14	SPS_D	General Indication		
Ind15	SPS_D	General Indication		
Ind16	SPS_D	General Indication		
Ind17	SPS_D	General Indication		

Attribute	Attr. Type	Explanation	T	X
Ind18	SPS_D	General Indication		
Ind19	SPS_D	General Indication		
Ind20	SPS_D	General Indication		
Ind21	SPS_D	General Indication		
Ind22	SPS_D	General Indication		
Ind23	SPS_D	General Indication		
Ind24	SPS_D	General Indication		
Ind25	SPS_D	General Indication		
Ind26	SPS_D	General Indication		
Ind27	SPS_D	General Indication		
Ind28	SPS_D	General Indication		
Ind29	SPS_D	General Indication		
Ind30	SPS_D	General Indication		
Ind31	SPS_D	General Indication		
Ind32	SPS_D	General Indication		
Ind33	SPS_D	General Indication		
Ind34	SPS_D	General Indication		
Ind35	SPS_D	General Indication		
Ind36	SPS_D	General Indication		
Ind37	SPS_D	General Indication		
Ind38	SPS_D	General Indication		
Ind39	SPS_D	General Indication		
Ind40	SPS_D	General Indication		
Ind41	SPS_D	General Indication		
Ind42	SPS_D	General Indication		
Ind43	SPS_D	General Indication		

1.4.12 LOGICAL NODE: GGIO_IND_DPS_8

Description: Generic Process I/O (w.r.t 8 Dual Point Status Indication Elements)

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
DPCSO1	DPC_STATUS_D	Double Point Status		
DPCSO2	DPC_STATUS_D	Double Point Status		
DPCSO3	DPC_STATUS_D	Double Point Status		
DPCSO4	DPC_STATUS_D	Double Point Status		
DPCSO5	DPC_STATUS_D	Double Point Status		
DPCSO6	DPC_STATUS_D	Double Point Status		
DPCSO7	DPC_STATUS_D	Double Point Status		
DPCSO8	DPC_STATUS_D	Double Point Status		

1.4.13 LOGICAL NODE: GGIO_USER_ALM_32

Description: Generic Process I/O

LN Class: GGIO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Alm1	SPS_D	General single alarm		
Alm2	SPS_D	General single alarm		
Alm3	SPS_D	General single alarm		
Alm4	SPS_D	General single alarm		
Alm5	SPS_D	General single alarm		
Alm6	SPS_D	General single alarm		
Alm7	SPS_D	General single alarm		
Alm8	SPS_D	General single alarm		
Alm9	SPS_D	General single alarm		
Alm10	SPS_D	General single alarm		
Alm11	SPS_D	General single alarm		
Alm12	SPS_D	General single alarm		
Alm13	SPS_D	General single alarm		
Alm14	SPS_D	General single alarm		
Alm15	SPS_D	General single alarm		
Alm16	SPS_D	General single alarm		
Alm17	SPS_D	General single alarm		
Alm18	SPS_D	General single alarm		
Alm19	SPS_D	General single alarm		
Alm20	SPS_D	General single alarm		
Alm21	SPS_D	General single alarm		
Alm22	SPS_D	General single alarm		
Alm23	SPS_D	General single alarm		
Alm24	SPS_D	General single alarm		
Alm25	SPS_D	General single alarm		
Alm26	SPS_D	General single alarm		
Alm27	SPS_D	General single alarm		
Alm28	SPS_D	General single alarm		
Alm29	SPS_D	General single alarm		
Alm30	SPS_D	General single alarm		
Alm31	SPS_D	General single alarm		
Alm32	SPS_D	General single alarm		

1.4.14 LOGICAL NODE: LCCH_SYSTEM

Description: Physical Communication Channel Supervision

LN Class: LCCH

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
ChLiv	SPS_D	If true, channel is receiving telegrams within a specified time interval 'ChLivTms'. In case of a redundancy protocol this refers to channel A.		

Attribute	Attr. Type	Explanation	T	X
RedChLiv	SPS_D	If true, redundant channel is receiving telegrams within a specified time interval 'ChLivTms' or determined by other criteria. In case of a redundancy protocol this refers to channel B.		

1.4.15 LOGICAL NODE: LCCH_SYSTEM_ENG_PORT

Description: Physical Communication Channel Supervision

LN Class: LCCH

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
ChLiv	SPS_D	If true, channel is receiving telegrams within a specified time interval 'ChLivTms'. In case of a redundancy protocol this refers to channel A.		

1.4.16 LOGICAL NODE: LGOS_SYSTEM

Description: Monitoring of GOOSE Messages

LN Class: LGOS

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
St	SPS_WD	Status of the subscription (True = active, False=not active)		
SimSt	SPS_WD	Status showing that really Sim messages are received and accepted		
ConfRevNum	INS_BASIC_PRIV	Expected configuration revision number		
RxConfRevNum	INS_BASIC_PRIV	Configuration revision number of the received messages. If no telegram is received, the attribute 'q.validity' is set to 'invalid'		
GoCBRef	ORG_SRC_REF	Reference to the subscribed GOOSE control block		
OoSeqGo	SPS_WD_PRIV	Out of order GOOSE indication		X

1.4.17 LOGICAL NODE: LLN0_STANDARD

Description: General Logical Node 0

LN Class: LLN0

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LLNO	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
GrRef	ORG_SRC_REF	Reference to a higher level logical device		

1.4.18 LOGICAL NODE: LLN0_STANDARD_CBFAIL

Description: Logical Node 0 in CBFail

LN Class: LLN0

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LLNO	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
GrRef	ORG_SRC_REF	Reference to a higher level logical device		

1.4.19 LOGICAL NODE: LLN0_STANDARD_MEA

Description: Measurements Logical Node 0

LN Class: LLN0

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LLNO_MEA	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
GrRef	ORG_SRC_REF	Reference to a higher level logical device		

1.4.20 LOGICAL NODE: LLN0_STANDARD_WITH_CTRLMOD

Description: Logical Node 0

LN Class: LLN0

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LLNO	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Mod	ENC_CTRL_LD_MOD_2	Mode		
GrRef	ORG_SRC_REF	Reference to a higher level logical device		

1.4.21 LOGICAL NODE: LLN0_SYSTEM

Description: System Logical Node 0

LN Class: LLN0

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LLNO	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Mod	ENC_CTRL_LD_MOD	Mode		
LocKey	SPS_WD	Local operation for complete logical device		
Loc	SPS_WD	Local control behaviour		
LocSta	SPC_CONTROL	Switching authority at station level		
LEDRs	SPC_CONTROL	LED reset	T	
MltLev	SPG_WD	Select mode of authority for local control		
OrdRun	SPS_WD_PRIV	Indicate IED is operating a Control Object		X
SyncSt	SPS_WD_PRIV	Indicate time synchronisation in the IED is active/inactive		X
MltLevEna	SPS_WD_PRIV	Multi-level enabled		X

1.4.22 LOGICAL NODE: LPHD_STANDARD

Description: Px40 Physical Device Information

LN Class: LPHD

Attribute	Attr. Type	Explanation	T	X
PhyNam	DPL_STANDARD	Physical device name plate		
PhyHealth	ENS_HEALTH	Physical device health		
Proxy	SPS_D	Indicates if this LN is a proxy		
PwrUp	SPS_D	Power up detected		

1.4.23 LOGICAL NODE: LPHD_SYSTEM

Description: Px40 Physical Device Information (Used for Logical Device System Only)

LN Class: LPHD

Attribute	Attr. Type	Explanation	T	X
PhyNam	DPL_STANDARD	Physical device name plate		
PhyHealth	ENS_HEALTH	Physical device health		
Proxy	SPS_D	Indicates if this LN is a proxy		
PwrUp	SPS_D	Power up detected		
Sim	SPC_CONTROL	Receive simulated GOOSE or simulated SV		

1.4.24 LOGICAL NODE: LSVS_SYSTEM

Description: Sampled Value Subscription

LN Class: LSVS

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
St	SPS_WD	Status of the subscription (True = active, False = not active)		
SvCRef	ORG_SRC_REF	Reference to the subscribed SV control block		

1.4.25 LOGICAL NODE: LTIM_SYSTEM

Description: Time Management

LN Class: LTIM

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
TmDT	SPS_WD	the daylight saving time is in effect now for this location		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
TmOfsTmm	ING_SET_TM	Offset of local time from UTC		
TmUseDT	SPG_SP	location is using daylight saving time		
TmChgDT	TSG_SP	Local time of next change to daylight saving time		
TmChgST	TSG_SP	Local time of next change to standard time		

1.4.26 LOGICAL NODE: LTMS_SYSTEM

Description: Time Master Supervision

LN Class: LTMS

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
TmAcc	INS_BASIC	Number of significant bits in the Fraction of Second in the time accuracy part of the time stamp		
TmSrc	VSS_WD	Current time source		
TmSrcTyp	ENS_CLK_SRC_KIND	Type of the clock source		
TmSyn	ENS_CLK_SYNC_KIND	Time synchronized according to IEC 61850-9-2		
TmChSt1	SPS_WD	If true, time channel n is receiving time msgs within a specified time interval		
TmSynLkd	ENS_CLK_SYNC_LK	Locked status of clock synchronisation.		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		

1.4.27 LOGICAL NODE: MLFR_FAULT_RECORD_NODIF_CB2

Description: Measurements of Fault Record without Differential Protection

LN Class: MLFR

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN_PRIV	Name Plate		
Beh	ENS_BEH_THREE_STATUS_DN	Behaviour		
Health	ENS_HEALTH_DN	Health		
AFIt	WYE_SEG_ANG_NEU_D_PRIV	Fault current		X
AmFlt	CMV_MAG_ANG_FLOAT	Fault mutual current		X
CB1OpTim	MV_FLOAT_PRIV	CB1 operate Time		X
CB2OpTim	MV_FLOAT_PRIV	CB2 operate Time		X
FltDur	MV_FLOAT_PRIV	Fault duration		X
PhVFlt	WYE_SEG_ANG_NEU_D_PRIV_1	Fault voltage		X
RlyTrTim	MV_FLOAT_PRIV	Relay trip time		X
V1Rem	CMV_MAG_ANG_FLOAT	Remote end V1		X

1.4.28 LOGICAL NODE: MLFR_PRE_FAULT

Description: Measurements of Fault Record

LN Class: MLFR

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN_PRIV	Name Plate		
Beh	ENS_BEH_THREE_STATUS_DN	Behaviour		
Health	ENS_HEALTH_DN	Health		
Hz	MV_FLOAT_PRIV	System frequency		X
AmPreFlt	CMV_MAG_ANG_FLOAT_PRIV	Prefault mutual current		X
APreFlt	WYE_SEG_ANG_RES_D_PRIV	Prefault current		X
PhVPreFlt	WYE_SEG_ANG_RES_D_PRIV	Prefault voltage		X

1.4.29 LOGICAL NODE: MMTR_PRIV

Description: Metering

LN Class: MMTR

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
TotWh	BCR_PRIV	Net real energy since last reset		
TotVArh	BCR_PRIV	Net reactive energy since last reset		
SupWh	BCR_PRIV	Real energy supply (Energy flow towards bus bar)		
SupVArh	BCR_PRIV	Reactive energy supply (Energy flow towards bus bar)		
DmdWh	BCR_PRIV	Real energy demand (Energy flow from bus bar)		
DmdVArh	BCR_PRIV	Reactive energy demand (Energy flow from bus bar)		
MTRRs	SPC_CTRL_PRIV	Reset Energy Meters		X

1.4.30 LOGICAL NODE: MMXU_FOURIER_CB2_EXT

Description: Standard Measurements for CB2 (w.r.t Fourier Values Including Df/Dt)

LN Class: MMXU

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
TotW	MV_FLOAT	Total active power (Total P)		
TotVAr	MV_FLOAT	Total reactive power (Total Q)		
TotVA	MV_FLOAT	Total apparent power (Total S)		
TotPF	MV_FLOAT	Average power factor (Total PF)		
Hz	MV_FLOAT	Frequency		
PPV	DEL_SEG_ANG	Phase to Phase voltages		
PhV	WYE_SEG_ANG_D	Phase to Ground voltages		
A	WYE_SEG_ANG_NEU_RES_D	Phase currents		
W	WYE_SEG	Phase active power (P)		
VAr	WYE_SEG	Phase reactive power (Q)		
VA	WYE_SEG	Phase apparent power (S)		
PF	WYE_SEG	Phase power factor		
ACurTrans1	WYE_SEG_ANG_D_PRIV	Phase Currents (CT1)		X
ACurTrans2	WYE_SEG_ANG_D_PRIV	Phase Currents (CT2)		X
AMut	WYE_NEU_ANG_D_PRIV	Phase currents (Mutual Magnitude)		X
ASef	WYE_NEU_ANG_D_PRIV	Phase currents (ISEF Magnitude)		X
DfDt	MV_FLOAT_PRIV	The measurement for Df/Dt		X
V1	WYE_RES_ANG_D_NS	VN Derived Magnitude Angle		X
V2	WYE_RES_ANG_D_NS	VN Measured Magnitude Angle		X

1.4.31 LOGICAL NODE: MMXU_METER_AV

Description: Metering Statistics (w.r.t Current, Real + Reactive Power - Average Values)

LN Class: MMXU

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
CicExp	SPS_WD	Calculation period expired	T	
CicMth	ENG_SET_WD_CLCMTH	Calculation method of statistical data objects		
CicMod	ENG_SET_WD_CLCMOD	Calculation mode		
CicIntvTyp	ENG_SET_WD_CLCINTVTYP	Calculation interval type		
CicIntvPer	ING_SET_WD	Number of units to consider to calculate the calculation interval duration		
AvWPhs	MV_FLOAT_D	Arithmetic average of the magnitude of active power of the 3 phases		
AvVArPhs	MV_FLOAT_D	Arithmetic average of the magnitude of reactive power of the 3 phases		
AvAPhsA	MV_FLOAT_D_PRIV	Arithmetic average of the magnitude of Ia current		X
AvAPhsB	MV_FLOAT_D_PRIV	Arithmetic average of the magnitude of Ib current		X
AvAPhsC	MV_FLOAT_D_PRIV	Arithmetic average of the magnitude of Ic current		X

1.4.32 LOGICAL NODE: MMXU_METER_MAX

Description: Standard Measurements (w.r.t Current, Real + Reactive Power - Max Values)

LN Class: MMXU

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
CicExp	SPS_WD	Calculation period expired	T	
CicMth	ENG_SET_WD_CLCMTH	Calculation method of statistical data objects		
CicMod	ENG_SET_WD_CLCMOD	Calculation mode		
MaxWPhs	MV_FLOAT_D	Maximum magnitude of active power of the 3 phases		
MaxVArPhs	MV_FLOAT_D	Maximum magnitude of reactive power of the 3 phases		
MaxAPhsA	MV_FLOAT_D_PRIV	Maximum magnitude of Ia current		X
MaxAPhsB	MV_FLOAT_D_PRIV	Maximum magnitude of Ib current		X
MaxAPhsC	MV_FLOAT_D_PRIV	Maximum magnitude of Ic current		X

1.4.33 LOGICAL NODE: MMXU_RMS

Description: Standard Measurements (w.r.t RMS Values)

LN Class: MMXU

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
CicMth	ENG_SET_WD_CLCMTH	Calculation method of statistical data objects		
PhV	WYE_SEG_D	Phase to Ground voltages		
A	WYE_SEG_D	Phase currents		

1.4.34 LOGICAL NODE: MSQI_ALL

Description: Sequence and Imbalance (w.r.t Pos, Neg, Zero)

LN Class: MSQI

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
SeqA	SEQ_MAG_ANG	Positive, Negative and Zero sequence current		
SeqV	SEQ_MAG_ANG	Positive, Negative and Zero sequence voltage		

1.4.35 LOGICAL NODE: MSQI_VOLTAGE

Description: Sequence and Imbalance (w.r.t Pos, Neg, Zero Voltage Only)

LN Class: MSQI

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health	T	
SeqV	SEQ_MAG_ANG	Positive, Negative and Zero sequence voltage		

1.4.36 LOGICAL NODE: PDIF_NEU

Description: Differential (w.r.t Neutral)

LN Class: PDIF

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Op	ACT_NEU	Operate	T	

1.4.37 LOGICAL NODE: PDOP_BASIC

Description: Directional Overpower

LN Class: PDOP

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Mod	ENC_MOD_TWO_STATUS	Mode		
Str	ACD_SEG	Start		
Op	ACT_SEG	Operate	T	

1.4.38 LOGICAL NODE: PDUP_BASIC

Description: Directional Underpower

LN Class: PDUP

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		

Attribute	Attr. Type	Explanation	T	X
Health	ENS_HEALTH	Health		
Str	ACD_SEG	Start		
Op	ACT_SEG	Operate	T	

1.4.39 LOGICAL NODE: PFRC_NO_SEG

Description: Rate of Change of Frequency (w.r.t No Phase Segregation)

LN Class: PFRC

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NO_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

1.4.40 LOGICAL NODE: PSDE_NEU

Description: Sensitive Directional Earthfault

LN Class: PSDE

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NEU	Start		
Op	ACT_NEU	Operate	T	

1.4.41 LOGICAL NODE: PTEF_NEU

Description: Transient Earth Fault (w.r.t Neutral)

LN Class: PTEF

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NEU	Start (transient earth fault)		
Op	ACT_NEU	Operate (transient earth fault)	T	

1.4.42 LOGICAL NODE: PTOC_NEU

Description: Timed Overcurrent (w.r.t Neutral)

LN Class: PTOC

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NEU	Start		
Op	ACT_NEU	Operate	T	

1.4.43 LOGICAL NODE: PTOC_NO_SEG

Description: Timed Overcurrent (w.r.t No Phase Segregation)

LN Class: PTOC

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NO_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

1.4.44 LOGICAL NODE: PTOC_SEG

Description: Timed Overcurrent (w.r.t Phase Segregation)

LN Class: PTOC

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_SEG	Start		
Op	ACT_SEG	Operate	T	

1.4.45 LOGICAL NODE: PTOF_NO_SEG

Description: Overfrequency (w.r.t No Phase Segregation)

LN Class: PTOF

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NO_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

1.4.46 LOGICAL NODE: PTOV_NEU

Description: Overvoltage (w.r.t Neutral)

LN Class: PTOV

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NO_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

1.4.47 LOGICAL NODE: PTOV_NO_SEG

Description: Overvoltage (w.r.t No Phase Segregation)

LN Class: PTOV

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NO_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

1.4.48 LOGICAL NODE: PTOV_SEG

Description: Overvoltage (w.r.t Phase Segregation)

LN Class: PTOV

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_SEG	Start		
Op	ACT_SEG	Operate	T	

1.4.49 LOGICAL NODE: PTRC_GLOBAL

Description: Protection Trip for Global Protection Conditioning

LN Class: PTRC

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Tr	ACT_SEG	Trip		
Op	ACT_SEG_NEU	Operate (combination of subscribed Op from protection functions)		
Str	ACD_SEG_NEU	Sum of all starts of all connected Logical Nodes		

1.4.50 LOGICAL NODE: PTRC_INDIVID_NO_SEG

Description: Protection Trip for Individual Protection Conditioning

LN Class: PTRC

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Op	ACT_NO_SEG	Operate (combination of subscribed Op from protection functions)		
Str	ACD_NO_SEG	Sum of all starts of all connected Logical Nodes		

1.4.51 LOGICAL NODE: PTTR_NO_SEG

Description: Thermal Overload (w.r.t No Phase Segregation)

LN Class: PTTR

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Op	ACT_NO_SEG	Operate	T	
AlmThm	SPS_WD	Thermal alarm		
Amp	MV_FLOAT	Current for thermal load model		
TmpRl	MV_FLOAT	Relation between temperature and maximum temperature		
MTRRs	SPC_CTRL_PRIV	Reset Thermal State		X

1.4.52 LOGICAL NODE: PTUF_NO_SEG

Description: Underfrequency (w.r.t No Phase Segregation)

LN Class: PTUF

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_NO_SEG	Start		
Op	ACT_NO_SEG	Operate	T	

1.4.53 LOGICAL NODE: PTUV_SEG

Description: Undervoltage (w.r.t Phase Segregation)

LN Class: PTUV

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Str	ACD_SEG	Start		
Op	ACT_SEG	Operate	T	

1.4.54 LOGICAL NODE: RBRF_EXTTRIP

Description: Breaker Failure (w.r.t External Tripping)

LN Class: RBRF

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_FOUR_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
OpEx	ACT_NO_SEG	Breaker failure trip ("External trip")	T	

1.4.55 LOGICAL NODE: RDRE_BASIC

Description: Disturbance Recorder Function (w.r.t Mandatory Attributes Only)

LN Class: RDRE

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
RcdMade	SPS_WD	Recording made		
FltNum	INS_BASIC	Fault number		
RcdStr	SPS_WD	Recording started		
RcdTrg	SPC_CONTROL	Trigger recorder		
MemClr	SPC_CONTROL	Clear memory	T	

1.4.56 LOGICAL NODE: RFLO_BASIC

Description: Fault Locator (w.r.t Mandatory Attributes Only)

LN Class: RFLO

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
FltLoop	ENS_PHASE_SEL	Fault loop		
FltZ	CMV_MAG_FLOAT	Fault impedance		
FltDiskm	MV_FLOAT	Fault distance in km		

1.4.57 LOGICAL NODE: RREC_NO_SEG

Description: Autoreclosing (w.r.t No Phase Segregation)

LN Class: RREC

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
RecCyc	INS_BASIC	Actual Reclose Cycle		
OpCls	ACT_NO_SEG	Operation "Close Switch" issued to close circuit breaker		
AutoRecSt	ENS_AUTORECST	Auto reclosing status		
MaxCyc	ING_SET_TM	Max number of reclose cycles		

1.4.58 LOGICAL NODE: RSYN_DIFCLC_ENH

Description: Synchronism-check/Synchronising (w.r.t Calculated Differential Measurements)

LN Class: RSYN

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
Rel	SPS_WD	Release		
VInd	SPS_WD	Voltage difference indicator		
AngInd	SPS_WD	Angle difference indicator		

Attribute	Attr. Type	Explanation	T	X
HzInd	SPS_WD	Frequency difference indicator		
DiffVClc	MV_FLOAT	Calculated difference in voltage		
DiffHzClc	MV_FLOAT	Calculated difference in frequency		
DiffAngClc	MV_FLOAT	Calculated difference of phase angle		

1.4.59 LOGICAL NODE: TVTR_SYSTEM

Description: Voltage Transformer

LN Class: TVTR

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
EEName	DPL_PRIV	External equipment name plate		
EEHealth	ENS_HEALTH	External equipment health		
FuFail	SPS_WD	TVTR fuse failure		
VRtg	ASG_SP_FLOAT	Rated Voltage		
HzRtg	ASG_SP_INT	Rated frequency		
Rat	ASG_SP_RAT	Winding ratio of external voltage transformer (transducer) if applicable		

1.4.60 LOGICAL NODE: XCBR_BASIC

Description: Circuit Breaker (w.r.t Mandatory Attributes Only)

LN Class: XCBR

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
EEHealth	ENS_HEALTH	External equipment health		
Loc	SPS_WD	Local operation		
OpCnt	INS_BASIC	Operation counter		
CBOpCap	ENS_CBCAP	Circuit Breaker operating capability		
SumSwARs	BCR_PRIV	Sum of switched amperes, resettable		
Pos	DPC_STATUS	Switch position		
BlkOpn	SPC_STATUS	Block opening		
BlkCls	SPC_STATUS	Block closing		

1.4.61 LOGICAL NODE: XSWI_BASIC

Description: Circuit Switch (w.r.t Switch Status and Control)

LN Class: XSWI

Attribute	Attr. Type	Explanation	T	X
NamPlt	LPL_LN	Name Plate		
Beh	ENS_BEH_THREE_STATUS	Behaviour		
Health	ENS_HEALTH	Health		
EEHealth	ENS_HEALTH	External equipment health		
Loc	SPS_WD	Local control behaviour		
OpCnt	INS_BASIC	Operation counter		
SwTyp	ENS_SWI_TYPE	Switch type		

Attribute	Attr. Type	Explanation	T	X
SwOpCap	ENS_SWOPCAP	Switch operating capability		
Pos	DPC_STATUS	Switch position		
BlkOpn	SPC_STATUS	Block opening		
BlkCls	SPC_STATUS	Block closing		

1.5 COMMON DATA CLASS DEFINITIONS

The definition tables for each of the Common Data Classes used in the Logical Node definitions are presented in the following sub-sections.

From an application point-of-view the data attributes of a Common Data Class are classified according to their specific use. The characterization of data attributes, and the services that they support/provide, will be through the use of 'Functional Constraints'. The Functional Constraints are specified by the table below:

FC Name	Semantic	Source Definition
BL	Blocking	IEC61850-7-2-2010
BR	Buffered reports	IEC61850-7-2
CF	Configuration	IEC61850-7-2
CO	Control	IEC61850-7-2
DC	Description	IEC61850-7-2
EX	Extended Definition	IEC61850-7-2
GO	GOOSE Control	IEC61850-7-2
GS	GSSE Control (UCA2 GOOSE)	IEC61850-7-2
LG	Logging	IEC61850-7-2
MS	Multicast sampled value control	IEC61850-7-2
MX	Measurands (Analogue values)	IEC61850-7-2
OR	Operate received	IEC61850-7-2-2010
RP	Unbuffered reports	IEC61850-7-2
SE	Setting Group Editable	IEC61850-7-2
SG	Setting Group	IEC61850-7-2
SP	Set Point	IEC61850-7-2
SR	Service response	IEC61850-7-2-2010
ST	Status Information	IEC61850-7-2
SV	Substitution Values	IEC61850-7-2
US	Unicast sampled value control	IEC61850-7-2
XX	Data attribute service parameters	IEC61850-7-2

1.5.1 COMMON DATA CLASS: ACD_NEU

Description: Directional Protection Activation Information (w.r.t Neutral)

CDC Class: ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	general
dirGeneral	ENUMERATED8 (MMS Type: INT8)	ST	FaultDirectionKind	General direction (unknown, forward, backward or both)	dirGeneral
neut	BOOLEAN	ST		Trip or start event with earth current has happened	neut
dirNeut	ENUMERATED8 (MMS Type: INT8)	ST	PhaseFaultDirectionKin	Earth current direction (unknown, forward or backward)	dirNeut
dq	Quality	ST		Quality of the protection activation information	dq
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	t

1.5.2 COMMON DATA CLASS: ACD_NO_SEG

Description: Directional Protection Activation Information (w.r.t No Phase Segregation)

CDC Class: ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
dirGeneral	ENUMERATED8 (MMS Type: INT8)	ST	dir	General direction (unknown, forward, backward or both)	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

1.5.3 COMMON DATA CLASS: ACD_SEG

Description: Directional Protection Activation Information (w.r.t Phase Segregation)

CDC Class: ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
dirGeneral	ENUMERATED8 (MMS Type: INT8)	ST	FaultDirectionKind	General direction (unknown, forward, backward or both)	
phsA	BOOLEAN	ST		Trip or start event of Phase A has happened	
dirPhsA	ENUMERATED8 (MMS Type: INT8)	ST	PhaseFaultDirectionKin	Phase A direction (unknown, forward or backward)	
dphsB	BOOLEAN	ST		Trip or start event of Phase B has happened	
dirPhsB	ENUMERATED8 (MMS Type: INT8)	ST	PhaseFaultDirectionKin	Phase B direction (unknown, forward or backward)	
dphsC	BOOLEAN	ST		Trip or start event of Phase C has happened	
dirPhsC	ENUMERATED8 (MMS Type: INT8)	ST	PhaseFaultDirectionKin	Phase C direction (unknown, forward or backward)	
dq	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

1.5.4 COMMON DATA CLASS: ACD_SEG_NEU

Description: Directional Protection Activation Information (w.r.t Phase Segregation + Neutral)

CDC Class: ACD

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
dirGeneral	ENUMERATED8 (MMS Type: INT8)	ST	dir	General direction (unknown, forward, backward or both)	
phsA	BOOLEAN	ST		Trip or start event of Phase A has happened	
dirPhsA	ENUMERATED8 (MMS Type: INT8)	ST	dir_3	Phase A direction (unknown, forward or backward)	
phsB	BOOLEAN	ST		Trip or start event of Phase B has happened	
dirPhsB	ENUMERATED8 (MMS Type: INT8)	ST	dir_3	Phase B direction (unknown, forward or backward)	
phsC	BOOLEAN	ST		Trip or start event of Phase C has happened	
dirPhsC	ENUMERATED8 (MMS Type: INT8)	ST	dir_3	Phase C direction (unknown, forward or backward)	
neut	BOOLEAN	ST		Trip or start event with earth current has happened	
dirNeut	ENUMERATED8 (MMS Type: INT8)	ST	dir_3	Earth current direction (unknown, forward or backward)	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

1.5.5 COMMON DATA CLASS: ACT_NEU

Description: Protection Activation Information (w.r.t Neutral)

CDC Class: ACT

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
neut	BOOLEAN	ST		Trip or start event with earth current has happened	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

1.5.6 COMMON DATA CLASS: ACT_NO_SEG

Description: Protection Activation Information (w.r.t No Phase Segregation)

CDC Class: ACT

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

1.5.7 COMMON DATA CLASS: ACT_SEG

Description: Protection Activation Information (w.r.t Phase Segregation)

CDC Class: ACT

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
phsA	BOOLEAN	ST		Trip or start event of Phase A has happened	
phsB	BOOLEAN	ST		Trip or start event of Phase B has happened	
phsC	BOOLEAN	ST		Trip or start event of Phase C has happened	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

1.5.8 COMMON DATA CLASS: ACT_SEG_NEU

Description: Protection Activation Information (w.r.t Phase Segregation + Neutral)

CDC Class: ACT

Attribute	Type	FC	Enumeration	Comment	X
general	BOOLEAN	ST		Trip or start has happened	
phsA	BOOLEAN	ST		Trip or start event of Phase A has happened	
phsB	BOOLEAN	ST		Trip or start event of Phase B has happened	
phsC	BOOLEAN	ST		Trip or start event of Phase C has happened	
neut	BOOLEAN	ST		Trip or start event with earth current has happened	
q	Quality	ST		Quality of the protection activation information	
t	TimeStamp	ST		Timestamp of the last change in state of protection activation information	

1.5.9 COMMON DATA CLASS: ASG_SP_FLOAT

Description: Analogue Setting for Float

CDC Class: ASG

Attribute	Type	FC	Enumeration	Comment	X
setMag	AnalogueValue_Float	SP		Setting value	
units	Unit_No_Multiplier	CF		Units of the attribute representing the data	
minVal	AnalogueValue_Float	CF		Minimum setting value	
maxVal	AnalogueValue_Float	CF		Maximum setting value	
stepSize	AnalogueValue_Float	CF		Setting step size (increment)	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.10 COMMON DATA CLASS: ASG_SP_INT

Description: Analogue Setting for Integer

CDC Class: ASG

Attribute	Type	FC	Enumeration	Comment	X
setMag	AnalogueValue_Int	SP		Setting value	
units	Unit_No_Multiplier	CF		Units of the attribute representing the data	
sVC	ScaledValueConfig	CF		Scaled value configuration	
minVal	AnalogueValue_Int	CF		Minimum setting value	
maxVal	AnalogueValue_Int	CF		Maximum setting value	
stepSize	AnalogueValue_Int	CF		Setting step size (increment)	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.11 COMMON DATA CLASS: ASG_SP_RAT

Description: Analogue Setting for Integer without Unit

CDC Class: ASG

Attribute	Type	FC	Enumeration	Comment	X
setMag	AnalogueValue_Int	SP		Setting value	
units	Unit_No_Multiplier	CF		Units of the attribute representing the data	
sVC	ScaledValueConfig	CF		Scaled value configuration	
minVal	AnalogueValue_Int	CF		Minimum setting value	
maxVal	AnalogueValue_Int	CF		Maximum setting value	
stepSize	AnalogueValue_Int	CF		Setting step size (increment)	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.12 COMMON DATA CLASS: BCR_PRIV

Description: Binary Counter Reading

CDC Class: BCR

Attribute	Type	FC	Enumeration	Comment	X
actVal	INT64	ST		Binary counter status represented as an integer	
q	Quality	ST		Quality of counter value	
t	TimeStamp	ST		Time of last counter change	
pulsQty	FLOAT32	CF		Magnitude of the counted value 'per count' (value = actVal x pulsQty)	

1.5.13 COMMON DATA CLASS: CMV_MAG_ANG_FLOAT

Description: Complex Measured Value (w.r.t Floating Point Magnitude and Angle)

CDC Class: CMV

Attribute	Type	FC	Enumeration	Comment	X
cVal	Vector_MagnitudeAngle_Float	MX		Deadbanded complex measured vector. Updated to the current value of instCVal when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
subEna	BOOLEAN	SV		Enable/disable substitution	
subCVal	Vector_MagnitudeAngle_Float	SV		Substituted measurement value for instCVal	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
units	Unit_Multiplier	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeConfig_DeadBand	CF		Measurement range configuration attributes	
dbRef	FLOAT32	CF		Defines deadband as an absolute value	

1.5.14 COMMON DATA CLASS: CMV_MAG_ANG_FLOAT_PRIV

Description: Complex Measured Value (Used for Extended DO)

CDC Class: CMV

Attribute	Type	FC	Enumeration	Comment	X
cVal	Vector_MagnitudeAngle_Float	MX		Deadbanded complex measured vector. Updated to the current value of instCVal when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
subEna	BOOLEAN	SV		Enable/disable substitution	
subCVal	Vector_MagnitudeAngle_Float	SV		Substituted measurement value for instCVal	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
units	Unit_Multiplier	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeConfig_DeadBand	CF		Measurement range configuration attributes	
dbRef	FLOAT32	CF		Defines deadband as an absolute value	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.15 COMMON DATA CLASS: CMV_MAG_FLOAT

Description: Complex Measured Value (w.r.t Floating Point Magnitude)

CDC Class: CMV

Attribute	Type	FC	Enumeration	Comment	X
cVal	Vector_Magnitude_Float	MX		Deadbanded complex measured vector. Updated to the current value of instCVal when the value has changed according to the configuration parameter db.	

Attribute	Type	FC	Enumeration	Comment	X
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
subEna	BOOLEAN	SV		Enable/disable substitution	
subCVal	Vector_Magnitude_Float	SV		Substituted measurement value for instCVal	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
units	Unit_Multiplier	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeConfig_DeadBand	CF		Measurement range configuration attributes	
dbRef	FLOAT32	CF		Defines deadband as an absolute value	

1.5.16 COMMON DATA CLASS: DEL_SEG_ANG

Description: Phase to Phase Measurements for a 3-Phase System (w.r.t Phase Segregation + Angle)

CDC Class: DEL

Attribute	Type	FC	Enumeration	Comment	X
pAsAB	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase A to Phase B	
pAsBC	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase B to Phase C	
pAsCA	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase C to Phase A	

1.5.17 COMMON DATA CLASS: DPC_CTRL

Description: Controllable Double Point (for CSWI.pos)

CDC Class: DPC

Attribute	Type	FC	Enumeration	Comment	X
ctlVal	BOOLEAN	CO		Control value (Off - FALSE, On - TRUE)	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	CODED_ENUM (MMS Type: _BSTR2)	ST	Dbpos	Status value of the data (Intermediate state, Off, On or Bad-state)	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
stSeld	BOOLEAN	ST		The controllable data is in the status "Selected"	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	CODED_ENUM (MMS Type: _BSTR2)	SV	Dbpos	Substitution value (Intermediate state, Off, On or Bad-state)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	
operTimeout	INT32U	CF		This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2	

1.5.18 COMMON DATA CLASS: DPC_STATUS

Description: Controllable Double Point (w.r.t Status Only)

CDC Class: DPC

Attribute	Type	FC	Enumeration	Comment	X
stVal	CODED_ENUM (MMS Type: _BSTR2)	ST	Dbpos	Status value of the data (Intermediate state, Off, On or Bad-state)	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	CODED_ENUM (MMS Type: _BSTR2)	SV	Dbpos	Substitution value (Intermediate state, Off, On or Bad-state)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	

1.5.19 COMMON DATA CLASS: DPC_STATUS_D

Description: Controllable Double Point (with Description)

CDC Class: DPC

Attribute	Type	FC	Enumeration	Comment	X
stVal	CODED_ENUM (MMS Type: _BSTR2)	ST	Dbpos	Status value of the data (Intermediate state, Off, On or Bad-state)	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	CODED_ENUM (MMS Type: _BSTR2)	SV	Dbpos	Substitution value (Intermediate state, Off, On or Bad-state)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.20 COMMON DATA CLASS: DPL_PRIV

Description: Device Name Plate For 'Teleprotection' Communications Channel

CDC Class: DPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRING255	DC		Name of the vendor	

1.5.21 COMMON DATA CLASS: DPL_STANDARD

Description: Standard Device Name Plate

CDC Class: DPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRING255	DC		Name of the vendor	
hwRev	VISIBLE_STRING255	DC		Hardware revision	
swRev	VISIBLE_STRING255	DC		Software revision	

Attribute	Type	FC	Enumeration	Comment	X
serNum	VISIBLE_STRING255	DC		Serial Number	
model	VISIBLE_STRING255	DC		Model Number	
location	VISIBLE_STRING255	DC		Physical location of device	

1.5.22 COMMON DATA CLASS: ENC_CTRL_LD_MOD

Description: Controllable Enumerated Status

CDC Class: ENC

Attribute	Type	FC	Enumeration	Comment	X
ctlVal	ENUMERATED32 (MMS Type: INT8)	CO	Mod_3	Control value	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	ENUMERATED32 (MMS Type: INT8)	ST	Mod_3	Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
stSeld	BOOLEAN	ST		The controllable data is in the status "Selected"	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	ENUMERATED32 (MMS Type: INT8)	SV	Mod_3	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	
operTimeout	INT32U	CF		This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.23 COMMON DATA CLASS: ENC_CTRL_LD_MOD_2

Description: Controllable Enumerated Status (Includes Three Status, Used for Child LD.LLN0)

CDC Class: ENC

Attribute	Type	FC	Enumeration	Comment	X
ctlVal	ENUMERATED32 (MMS Type: INT8)	CO	Mod_2	Control value	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	ENUMERATED32 (MMS Type: INT8)	ST	Mod_2	Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
stSeld	BOOLEAN	ST		The controllable data is in the status "Selected"	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	ENUMERATED32 (MMS Type: INT8)	SV	Mod_2	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	

Attribute	Type	FC	Enumeration	Comment	X
operTimeout	INT32U	CF		This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.24 COMMON DATA CLASS: ENC_MOD_TWO_STATUS

Description: Controllable Enumerated Status

CDC Class: ENC

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED32 (MMS Type: INT8)	ST	Mod_2	Status value of the mode used for LN which have two status	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	ENUMERATED32 (MMS Type: INT8)	SV	Mod_2	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	

1.5.25 COMMON DATA CLASS: ENG_SET_WD_CLCINTVTYP

Description: Enumerated Status Setting (for ClcIntvTyp)

CDC Class: ENG

Attribute	Type	FC	Enumeration	Comment	X
setVal	ENUMERATED8 (MMS Type: INT8)	SP	ClcIntvTyp	Setting value	

1.5.26 COMMON DATA CLASS: ENG_SET_WD_CLCMOD

Description: Enumerated Status Setting (for ClcMod)

CDC Class: ENG

Attribute	Type	FC	Enumeration	Comment	X
setVal	ENUMERATED8 (MMS Type: INT8)	SP	ClcMod	Setting value	

1.5.27 COMMON DATA CLASS: ENG_SET_WD_CLCMTH

Description: Enumerated Status Setting (for ClcMth)

CDC Class: ENG

Attribute	Type	FC	Enumeration	Comment	X
setVal	ENUMERATED8 (MMS Type: INT8)	SP	ClcMth	Setting value	

1.5.28 COMMON DATA CLASS: ENS_AUTORECST

Description: Enumerated Status

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	AutoRecSt	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	AutoRecSt	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.29 COMMON DATA CLASS: ENS_BEH_FOUR_STATUS

Description: Enumerated Behaviour Status (with 4 Status)

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	Beh_4	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	Beh_4	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.30 COMMON DATA CLASS: ENS_BEH_THREE_STATUS

Description: Enumerated Behaviour Status (with 3 Status)

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	Beh_3	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	Beh_3	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.31 COMMON DATA CLASS: ENS_BEH_THREE_STATUS_DN

Description: Enumerated Status (with 3 Status and dataNs Used for the Beh in the Extended LN)

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	Beh_3	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	Beh_3	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.32 COMMON DATA CLASS: ENS_CBCAP

Description: Enumerated Status (w.r.t CB Operating Capability)

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	BreakerOpCapabilityKind	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	BreakerOpCapabilityKind	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.33 COMMON DATA CLASS: ENS_CLK_SRC_KIND

Description: Enumerated Status for Time Src Type

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	ClockSourceKind	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	ClockSourceKind	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.34 COMMON DATA CLASS: ENS_CLK_SYNC_KIND

Description: Enumerated Status for Clock Sync Type

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	ClockSyncKind	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	ClockSyncKind	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.35 COMMON DATA CLASS: ENS_CLK_SYNC_LK

Description: Enumerated Status for ClockSyncLockingKind

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	ClockSyncLockKind	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	ClockSyncLockKind	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.36 COMMON DATA CLASS: ENS_HEALTH

Description: Enumerated Status

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	HealthKind	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	HealthKind	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.37 COMMON DATA CLASS: ENS_HEALTH_DN

Description: Enumerated Status (with dataNs Used for the Health in the Extended LN)

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	HealthKind	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	HealthKind	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.38 COMMON DATA CLASS: ENS_PHASE_SEL

Description: Enumerated Status

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	FaultLoopKind	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	FaultLoopKind	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.39 COMMON DATA CLASS: ENS_SWI_TYPE

Description: Enumerated Status

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	SwType	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	ENUMERATED8 (MMS Type: INT8)	SV	SwType	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.40 COMMON DATA CLASS: ENS_SWOPCAP

Description: Enumerated Status

CDC Class: ENS

Attribute	Type	FC	Enumeration	Comment	X
stVal	ENUMERATED8 (MMS Type: INT8)	ST	SwOpCap	The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	INT32 (MMS Type: INT8)	SV	SwOpCap	Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	

1.5.41 COMMON DATA CLASS: INC_MOD_STD

Description: Standard Controllable Integer Status (w.r.t Mode)

CDC Class: INC

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32	ST		Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	INT32	SV		Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	

1.5.42 COMMON DATA CLASS: ING_SET_TM

Description: Integer Status Setting

CDC Class: ING

Attribute	Type	FC	Enumeration	Comment	X
setVal	INT32	SP		Setting value	
minVal	INT32	CF		Minimum setting value	
maxVal	INT32	CF		Maximum setting value	
stepSize	INT32U	CF		Setting step size (increment)	

1.5.43 COMMON DATA CLASS: ING_SET_WD

Description: Integer Status Setting

CDC Class: ING

Attribute	Type	FC	Enumeration	Comment	X
setVal	INT32	SP		Setting value	

1.5.44 COMMON DATA CLASS: INS_BASIC

Description: Integer Status (w.r.t Mandatory Options Only)

CDC Class: INS

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32	ST		The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	INT32	SV		Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.45 COMMON DATA CLASS: INS_BASIC_PRIV

Description: Integer Status (Private in IEC61850V2.0)

CDC Class: INS

Attribute	Type	FC	Enumeration	Comment	X
stVal	INT32	ST		The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	INT32	SV		Substitution value	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.46 COMMON DATA CLASS: LPL_LLNO

Description: Logical Node 0 Name Plate

CDC Class: LPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRING255	DC		Name of the vendor	
swRev	VISIBLE_STRING255	DC		Software revision	
ldNs	VISIBLE_STRING255	EX		Logical Device name space	
d	VISIBLE_STRING255	DC		Description	
configRev	VISIBLE_STRING255	DC		Uniquely identifies the configuration of a local device instance	

1.5.47 COMMON DATA CLASS: LPL_LLNO_MEA

Description: Measurements Logical Node 0 name plate

CDC Class: LPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRING255	DC		Name of the vendor	
swRev	VISIBLE_STRING255	DC		Software revision	
ldNs	VISIBLE_STRING255	EX		Logical Device name space	
configRev	VISIBLE_STRING255	DC		Uniquely identifies the configuration of a local device instance	

1.5.48 COMMON DATA CLASS: LPL_LN

Description: Standard Logical Node Name Plate

CDC Class: LPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRING255	DC		Name of the vendor	
swRev	VISIBLE_STRING255	DC		Software revision	
d	VISIBLE_STRING255	DC		Description	

1.5.49 COMMON DATA CLASS: LPL_LN_PRIV

Description: Logical Node Name Plate (w.r.t GE Grid Solutions Extended)

CDC Class: LPL

Attribute	Type	FC	Enumeration	Comment	X
vendor	VISIBLE_STRING255	DC		Name of the vendor	
swRev	VISIBLE_STRING255	DC		Software revision	
InNs	VISIBLE_STRING255	EX		Logical Node name space	
d	VISIBLE_STRING255	DC		Description	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.50 COMMON DATA CLASS: MV_FLOAT

Description: Measured Value (w.r.t Floating Point Value)

CDC Class: MV

Attribute	Type	FC	Enumeration	Comment	X
mag	AnalogueValue_Float	MX		Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
subEna	BOOLEAN	SV		Enable/disable substitution	
subMag	AnalogueValue_Float	SV		Substituted measurement value for instMag	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
units	Unit_Multiplier	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeConfig_DeadBand	CF		Measurement range configuration attributes	
dbRef	FLOAT32	CF		Defines deadband size as an absolute value	

1.5.51 COMMON DATA CLASS: MV_FLOAT_D

Description: Measured Value (w.r.t Floating Point Value with Description)

CDC Class: MV

Attribute	Type	FC	Enumeration	Comment	X
mag	AnalogueValue_Float	MX		Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
subEna	BOOLEAN	SV		Enable/disable substitution	

Attribute	Type	FC	Enumeration	Comment	X
subMag	AnalogueValue_Float	SV		Substituted measurement value for instMag	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
units	Unit_Multiplier	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeConfig_DeadBand	CF		Measurement range configuration attributes	
dbRef	FLOAT32	CF		Defines deadband size as an absolute value	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.52 COMMON DATA CLASS: MV_FLOAT_D_PRIV

Description: Measured Value

CDC Class: MV

Attribute	Type	FC	Enumeration	Comment	X
mag	AnalogueValue_Float	MX		Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
subEna	BOOLEAN	SV		Enable/disable substitution	
subMag	AnalogueValue_Float	SV		Substituted measurement value for instMag	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
units	Unit	CF		Unit of the attribute representing the data	
db	INT32U	CF		Measurement deadband	
rangeC	RangeConfig_DeadBand	CF		Measurement range configuration attributes	
dbRef	FLOAT32	CF		Defines deadband size as an absolute value	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.53 COMMON DATA CLASS: MV_FLOAT_PRIV

Description: Measured Value (Used for Extended DO)

CDC Class: MV

Attribute	Type	FC	Enumeration	Comment	X
mag	AnalogueValue_Float	MX		Deadbanded magnitude of the instantaneous value of a measured value or harmonic value. Updated to the current value of instMag when the value has changed according to the configuration parameter db.	
q	Quality	MX		Quality of the measurement value	
t	TimeStamp	MX		Time deadbanded magnitude last exceeded its db configuration parameter	
subEna	BOOLEAN	SV		Enable/disable substitution	
subMag	AnalogueValue_Float	SV		Substituted measurement value for instMag	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
units	Unit	CF		Unit of the attribute representing the data	

Attribute	Type	FC	Enumeration	Comment	X
db	INT32U	CF		Measurement deadband	
rangeC	RangeConfig_DeadBand	CF		Measurement range configuration attributes	
dbRef	FLOAT32	CF		Defines deadband size as an absolute value	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.54 COMMON DATA CLASS: ORG_SRC_REF

Description: Object Reference Settings

CDC Class: ORG

Attribute	Type	FC	Enumeration	Comment	X
setSrcRef	ObjectReference	SP		The value of the object reference setting	

1.5.55 COMMON DATA CLASS: SEQ_MAG_ANG

Description: Sequence Components of a Measurement Value (w.r.t Magnitudes + Angles)

CDC Class: SEQ

Attribute	Type	FC	Enumeration	Comment	X
c1	CMV_MAG_ANG_FLOAT	--		Sequence component 1 (For semantic meaning see seqT)	
c2	CMV_MAG_ANG_FLOAT	--		Sequence component 2 (For semantic meaning see seqT)	
c3	CMV_MAG_ANG_FLOAT	--		Sequence component 3 (For semantic meaning see seqT)	
seqT	ENUMERATED8 (MMS Type: INT8)	MX	seqT	Sequence quantity measurement type (Pos-Neg-Zero or Dir-Quad-Zero)	

1.5.56 COMMON DATA CLASS: SPC_CONTROL

Description: Controllable Single Point

CDC Class: SPC

Attribute	Type	FC	Enumeration	Comment	X
ctlVal	BOOLEAN	CO		Control value (Off - FALSE, On - TRUE)	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	BOOLEAN	ST		Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
stSeld	BOOLEAN	ST		The controllable data is in the status "Selected"	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	BOOLEAN	SV		Substitution value (True or False)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	
operTimeout	INT32U	CF		This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2	

1.5.57 COMMON DATA CLASS: SPC_CTRL_PRIV

Description: Controllable Single Point (with Namespace)

CDC Class: SPC

Attribute	Type	FC	Enumeration	Comment	X
ctlVal	BOOLEAN	CO		Control value (Off - FALSE, On - TRUE)	
origin	Originator	ST		Originator of the last change of the controllable data	
stVal	BOOLEAN	ST		Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
stSeld	BOOLEAN	ST		The controllable data is in the status "Selected"	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	BOOLEAN	SV		Substitution value (True or False)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	
sboTimeout	INT32U	CF		Select Before Operate timeout period (in milliseconds)	
operTimeout	INT32U	CF		This attribute specifies the timeout used to supervise an operation according to the control model defined in IEC 61850-7-2	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.58 COMMON DATA CLASS: SPC_STATUS

Description: Controllable Single Point (w.r.t Status Only)

CDC Class: SPC

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		Status value of the data	
q	Quality	ST		Quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state of status value	
subEna	BOOLEAN	SV		Enable/disable substitution	
subVal	BOOLEAN	SV		Substitution value (True or False)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
ctlModel	ENUMERATED8 (MMS Type: INT8)	CF	ctlModel	Control model (Corresponding to the behaviour of the data)	

1.5.59 COMMON DATA CLASS: SPG_SP

Description: Single Point Setting

CDC Class: SPG

Attribute	Type	FC	Enumeration	Comment	X
setVal	BOOLEAN	SP		Setting value (Off - FALSE, On - TRUE)	

1.5.60 COMMON DATA CLASS: SPG_WD

Description: Single Point Setting

CDC Class: SPG

Attribute	Type	FC	Enumeration	Comment	X
setVal	BOOLEAN	SP		Setting value (Off - FALSE, On - TRUE)	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.61 COMMON DATA CLASS: SPS_D

Description: Standard Single Point Status (with Description)

CDC Class: SPS

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		The element status (TRUE or FALSE)	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	BOOLEAN	SV		Substitution value (TRUE or FALSE)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.62 COMMON DATA CLASS: SPS_WD

Description: Single Point Status (without Description)

CDC Class: SPS

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		The element status (TRUE or FALSE)	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	BOOLEAN	SV		Substitution value (TRUE or FALSE)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	

1.5.63 COMMON DATA CLASS: SPS_WD_PRIV

Description: Single Point Status (without Description with Name Space)

CDC Class: SPS

Attribute	Type	FC	Enumeration	Comment	X
stVal	BOOLEAN	ST		The element status (TRUE or FALSE)	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	
subEna	BOOLEAN	SV		Substitution enabled/disabled	
subVal	BOOLEAN	SV		Substitution value (TRUE or FALSE)	
subQ	Quality	SV		Value used to substitute the data attribute q	
subID	VISIBLE_STRING64	SV		Address of the device that made the substitution	

Attribute	Type	FC	Enumeration	Comment	X
blkEna	BOOLEAN	BL		If TRUE, the operator-blocked quality flag is set, and the process value no longer updated	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.64 COMMON DATA CLASS: TSG_SP

Description: Time Setting Group

CDC Class: TSG

Attribute	Type	FC	Enumeration	Comment	X
setCal	CalendarTime	SP		The value of a time setting, if the time is set with a calendar time	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.65 COMMON DATA CLASS: VSS_WD

Description: Visible String Status (without Description)

CDC Class: VSS

Attribute	Type	FC	Enumeration	Comment	X
stVal	VISIBLE_STRING255	ST		The element status	
q	Quality	ST		The quality of the status value	
t	TimeStamp	ST		Timestamp of the last change in state	

1.5.66 COMMON DATA CLASS: WYE_NEU_ANG_D_PRIV

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
neut	CMV_MAG_ANG_FLOAT	--		Measurement values for neutral input	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.67 COMMON DATA CLASS: WYE_RES_ANG_D_PRIV

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
res	CMV_MAG_ANG_FLOAT	--		Measurement values for the residual system current	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.68 COMMON DATA CLASS: WYE_RES_ANG_D_NS

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
neut	CMV_MAG_ANG_FLOAT	--		Measurement values for neutral input	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.69 COMMON DATA CLASS: WYE_SEG

Description: Phase to Ground Measurements for a 3-Phase System (w.r.t Phase Segregation)

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_FLOAT	--		Measurement values for Phase C	

1.5.70 COMMON DATA CLASS: WYE_SEG_ANG_D

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase C	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.71 COMMON DATA CLASS: WYE_SEG_ANG_D_PRIV

Description: Phase to Ground Measurements for a 3-Phase System

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase C	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.72 COMMON DATA CLASS: WYE_SEG_ANG_NEU_D_PRIV

Description: Phase to Ground Measurements for a 3-Phase System (Used for Extended DO)

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase C	
neut	CMV_MAG_FLOAT	--		Measurement values for neutral input	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.73 COMMON DATA CLASS: WYE_SEG_ANG_NEU_D_PRIV_1

Description: Phase to Ground Measurements for a 3-Phase System (Used for Private Data)

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase C	

Attribute	Type	FC	Enumeration	Comment	X
neut	CMV_MAG_ANG_FLOAT	--		Measurement values for neutral input	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.74 COMMON DATA CLASS: WYE_SEG_ANG_NEU_RES_D

Description: Phase to Ground Measurements for a 3-Phase System (w.r.t Phase Segregation + Neutral + Residual + Description)

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase C	
neut	CMV_MAG_ANG_FLOAT	--		Measurement values for neutral input	
res	CMV_MAG_ANG_FLOAT	--		Measurement values for the residual system current	
d	VISIBLE_STRING255	DC		Description of the status element	

1.5.75 COMMON DATA CLASS: WYE_SEG_ANG_RES_D_PRIV

Description: Phase to Ground Measurements for a 3-Phase System (Used for Extended DO)

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_ANG_FLOAT	--		Measurement values for Phase C	
res	CMV_MAG_ANG_FLOAT	--		Measurement values for the residual system current	
d	VISIBLE_STRING255	DC		Description of the status element	
dataNs	VISIBLE_STRING255	EX		Data name space	

1.5.76 COMMON DATA CLASS: WYE_SEG_D

Description: Phase to Ground Measurements for a 3-Phase System (w.r.t Phase Segregation + Description)

CDC Class: WYE

Attribute	Type	FC	Enumeration	Comment	X
phsA	CMV_MAG_FLOAT	--		Measurement values for Phase A	
phsB	CMV_MAG_FLOAT	--		Measurement values for Phase B	
phsC	CMV_MAG_FLOAT	--		Measurement values for Phase C	
d	VISIBLE_STRING255	DC		Description of the status element	

1.6 COMMON DATA ATTRIBUTE TYPE DEFINITIONS

Common data attribute types, known herein as components, are defined for use in the Common Data Classes defined in the sections above.

1.6.1 COMPONENT: ANALOGUEVALUE_FLOAT

Comment: General Analogue Value (w.r.t Floating Point Value)

Parent Type: AnalogueValue

Attribute	Type	Enumeration	Comment	X
f	FLOAT32		Floating point value	

1.6.2 COMPONENT: ANALOGUEVALUE_INT

Comment: General Analogue Value (w.r.t Integer)

Parent Type: AnalogueValue

Attribute	Type	Enumeration	Comment	X
i	INT32		32 bit signed integer value	

1.6.3 COMPONENT: CALENDARTIME

Comment: CalendarTime Type is Used to Define a Time Setting in Reference to the Calendar

Parent Type:

Attribute	Type	Enumeration	Comment	X
day	INT8U		The day	
hr	INT8U		The hour	
mn	INT8U		The minute	
month	ENUMERATED8 (MMS Type: INT8)	month	The month	
occ	INT16U		Occurrence of a calendar element	
occPer	ENUMERATED8 (MMS Type: INT8)	occPer	The repetition period of a calendar-based time setting	
occType	ENUMERATED8 (MMS Type: INT8)	occType	The kind of calendar element that is used for the occurrence	
weekDay	ENUMERATED8 (MMS Type: INT8)	weekDay	The weekday	

1.6.4 COMPONENT: ORIGINATOR

Comment: Originator of the Last Change of Data Attribute Representing the Value of a Controllable Data Object

Parent Type:

Attribute	Type	Enumeration	Comment	X
orCat	ENUMERATED8 (MMS Type: INT8)	orCategory	Originator category (Not-supported, bay-control, station-control, remote-control, automatic-bay, automatic-station, automatic-remote, maintenance or process)	
orIdent	OCTET_STRING64		Originator identification (Null value indicates unknown or not reported)	

1.6.5 COMPONENT: RANGECONFIG_DEADBAND

Comment: Measurement Range Configuration

Parent Type: RangeConfig

Attribute	Type	Enumeration	Comment	X
lLim	AnalogueValue_Float		Low range limit	
hLim	AnalogueValue_Float		High range limit	
llLim	AnalogueValue_Float		Low Low range limit	
max	AnalogueValue_Float		Maximum process measurement for which values of i and f are considered within limits	
min	AnalogueValue_Float		Minimum process measurement for which values of i and f are considered within limits	
hhLim	AnalogueValue_Float		High High range limit	

1.6.6 COMPONENT: SCALEDVALUECONFIG

Comment: Configuration of Analogue Value

Parent Type:

Attribute	Type	Enumeration	Comment	X
offset	FLOAT32		The offset of to apply to the integer analogue value	
scaleFact	FLOAT32		Scaling factor to apply to integer analogue values (i.e. via multiplication)	

1.6.7 COMPONENT: UNIT

Comment: SI Unit Definitions

Parent Type:

Attribute	Type	Enumeration	Comment	X
multiplier	ENUMERATED8 (MMS Type: INT8)	multiplier	Multiplier value, the default of which is 0 (i.e. multiplier = 1)	
SIUnit	ENUMERATED8 (MMS Type: INT8)	SIUnit	SI Unit	

1.6.8 COMPONENT: UNIT_MULTIPLIER

Comment: SI Unit Definitions

Parent Type: Unit

Attribute	Type	Enumeration	Comment	X
multiplier	ENUMERATED8 (MMS Type: INT8)	multiplier	Multiplier value, the default of which is 0 (i.e. multiplier = 1)	
SIUnit	ENUMERATED8 (MMS Type: INT8)	SIUnit	SI Unit	

1.6.9 COMPONENT: UNIT_NO_MULTIPLIER

Comment: SI Unit Definitions

Parent Type: Unit

Attribute	Type	Enumeration	Comment	X
SIUnit	ENUMERATED8 (MMS Type: INT8)	SIUnit	SI Unit	

1.6.10 COMPONENT: VECTOR_MAGNITUDE_FLOAT

Comment: Complex Vector (w.r.t Floating Point Magnitude Value)

Parent Type: Vector

Attribute	Type	Enumeration	Comment	X
mag	AnalogueValue_Float		The magnitude of the complex value	

1.6.11 COMPONENT: VECTOR_MAGNITUDEANGLE_FLOAT

Comment: Complex Vector (w.r.t Floating Point Magnitude and Angle Values)

Parent Type: Vector

Attribute	Type	Enumeration	Comment	X
mag	AnalogueValue_Float		The magnitude of the complex value	
ang	AnalogueValue_Float		The angle of the complex value (the unit is degrees)	

1.7 ENUMERATED TYPE DEFINITIONS

The following sub-sections specify the enumerations that are associated to some Common Data Class attributes. The definition of the enumerations are according to IEC 61850-7-3 and IEC 61850-7-4 unless otherwise stated.

1.7.1 ENUMERATED TYPE: ADDCAUSE

Description: AddCause

Ordinal	Semantic
0	Unknown
1	Not-supported
2	Blocked-by-switching-hierarchy
3	Select-failed
4	Invalid-position
5	Position-reached
6	Parameter-change-in-execution
7	Step-limit
8	Blocked-by-Mode
9	Blocked-by-process
10	Blocked-by-interlocking
11	Blocked-by-synchrocheck
12	Command-already-in-execution
13	Blocked-by-health
14	1-of-n-control
15	Abortion-by-cancel
16	Time-limit-over
17	Abortion-by-trip
18	Object-not-selected
19	Object-already-selected
20	No-access-authority
21	Ended-with-overshoot
22	Abortion-due-to-deviation
23	Abortion-by-communication-loss
24	Blocked-by-command
25	None
26	Inconsistent-parameters
27	Locked-by-other-client
20	No-access-authority
21	Ended-with-overshoot
22	Abortion-due-to-deviation
23	Abortion-by-communication-loss
24	Blocked-by-command

Ordinal	Semantic
25	None
26	Inconsistent-parameters
27	Locked-by-other-client

1.7.2 ENUMERATED TYPE: AUTORECST

Description: Auto-Reclose Status

Ordinal	Semantic
1	Ready
2	InProgress
3	Successful
4	WaitingForTrip
5	TripFromProtection
6	FaultDisappeared
7	WaitToComplete
8	CBclosed
9	CycleUnsuccessful
10	Unsuccessful
11	Aborted

1.7.3 ENUMERATED TYPE: BEH_3

Description: Behaviour Including 3 States

Ordinal	Semantic
1	on
3	test
4	test/blocked

1.7.4 ENUMERATED TYPE: BEH_4

Description: Behaviour Including 4 States

Ordinal	Semantic
1	on
3	test
4	test/blocked
5	off

1.7.5 ENUMERATED TYPE: BREAKEROPCAPABILITYKIND

Description: CB Operating Capability

Ordinal	Semantic
1	None
2	Open
3	Close-Open
4	Open-Close-Open
5	Close-Open-Close-Open
6	Open-Close-Open-Close-Open
7	more

1.7.6 ENUMERATED TYPE: CLCINTVTYP

Description: Calculation Interval Type

Ordinal	Semantic
1	MS
2	PER_CYCLE
3	CYCLE
4	DAY
5	WEEK
6	MONTH
7	YEAR
8	EXTERNAL

1.7.7 ENUMERATED TYPE: CLCMOD

Description: Calculation Mode

Ordinal	Semantic
1	TOTAL
2	PERIOD
3	SLIDING

1.7.8 ENUMERATED TYPE: CLCMTH

Description: Calculation Method of Statistical Data Objects

Ordinal	Semantic
1	UNSPECIFIED
2	TRUE_RMS
3	PEAK_FUNDAMENTAL
4	RMS_FUNDAMENTAL
5	MIN
6	MAX
7	AVG
8	SDV
9	PREDICTION
10	RATE

1.7.9 ENUMERATED TYPE: CLOCKSOURCEKIND

Description: Literals of ClockSourceKind

Ordinal	Semantic
1	Unknown
2	SNTP
3	PTP
4	IRIG-B
5	Substation internal

1.7.10 ENUMERATED TYPE: CLOCKSYNCKIND

Description: Literals of ClockSyncKind

Ordinal	Semantic
0	InternalClock
1	LocalAreaClock

Ordinal	Semantic
2	GlobalAreaClock

1.7.11 ENUMERATED TYPE: CLOCKSYNCKIND

Description: Literals of ClockSyncLockingKind

Ordinal	Semantic
1	Locked
2	Unlocked10s
3	Unlocked100s
4	Unlocked1000s
5	UnlockedMoreThan1000s

1.7.12 ENUMERATED TYPE: CTLMODEL

Description: Control Model

Ordinal	Semantic
0	status-only
1	direct-with-normal-security
2	sbo-with-normal-security
3	direct-with-enhanced-security
4	sbo-with-enhanced-security

1.7.13 ENUMERATED TYPE: DBPOS

Description: Switch Positions

Ordinal	Semantic
0	intermediate
1	off
2	on
3	bad

1.7.14 ENUMERATED TYPE: FAULTDIRECTIONKIND

Description: Direction

Ordinal	Semantic
0	unknown
1	forward
2	backward
3	both

1.7.15 ENUMERATED TYPE: FAULTLOOPKIND

Description: (RFLO) Designates the Kind of Fault Loop

Ordinal	Semantic
1	PhaseAtoGround
2	PhaseBtoGround
3	PhaseCtoGround
4	PhaseAtoB
5	PhaseBtoC
6	PhaseCtoA
7	Others

1.7.16 ENUMERATED TYPE: HEALTHKIND

Description: Literals of HealthKind

Ordinal	Semantic
1	Ok
2	Warning
3	Alarm

1.7.17 ENUMERATED TYPE: MOD_2

Description: Mode Including 2 States

Ordinal	Semantic
1	on
5	off

1.7.18 ENUMERATED TYPE: MOD_3

Description: Mode Including 3 States

Ordinal	Semantic
1	on
3	test
4	test/blocked

1.7.19 ENUMERATED TYPE: MONTH

Description: The Month

Ordinal	Semantic
0	reserved
1	January
2	February
3	March
4	April
5	May
6	June
7	July
8	August
9	September
10	October
11	November
12	December

1.7.20 ENUMERATED TYPE: MULTIPLIER

Description: Exponents of the Multiplier Value in Base 10

Ordinal	Semantic
-24	y
-21	z
-18	a
-15	f
-12	p
-9	n
-6	μ

Ordinal	Semantic
-3	m
-2	c
-1	d
0	
1	da
2	h
3	k
6	M
9	G
12	T
15	P
18	E
21	Z
24	Y

1.7.21 ENUMERATED TYPE: OCCPER

Description: The Repetition Period of a Calendar-Based Time Setting

Ordinal	Semantic
0	Hour
1	Day
2	Week
3	Month
4	Year

1.7.22 ENUMERATED TYPE: OCCTYPE

Description: The Kind of Calendar Element that is Used for the Occurrence

Ordinal	Semantic
0	Time
1	WeekDay
2	WeekOfYear
3	DayOfMonth
4	DayOfYear

1.7.23 ENUMERATED TYPE: ORCATEGORY

Description: orCategory

Ordinal	Semantic
0	not-supported
1	bay-control
2	station-control
3	remote-control
4	automatic-bay
5	automatic-station
6	automatic-remote
7	maintenance
8	process

1.7.24 ENUMERATED TYPE: PHASEFAULTDIRECTIONKIND

Description: Direction for Phase/Neutral

Ordinal	Semantic
0	unknown
1	forward
2	backward

1.7.25 ENUMERATED TYPE: SEQT

Description: Sequence Measurement Type

Ordinal	Semantic
0	pos-neg-zero
1	dir-quad-zero

1.7.26 ENUMERATED TYPE: SIUNIT

Description: SI Units Derived from ISO/IEC 1000

Ordinal	Semantic
-16	years
-15	months
-14	weeks
-13	V/s
-12	mins
-11	hours
-10	days
-9	°F
-8	ratio
-7	miles
-6	inches
-5	feet
-4	df/dt
-3	hz/s
-2	%
-1	pu
1	
-16	years
-15	months
-14	weeks
-13	V/s
-12	mins
-11	hours
-10	days
-9	°F
-8	ratio
-7	miles
-6	inches
-5	feet
-4	df/dt
-3	hz/s
-2	%
-1	pu

Ordinal	Semantic
1	
2	m
3	kg
4	s
5	A
6	K
7	mol
8	cd
9	deg
10	rad
11	sr
21	Gy
22	Bq
23	°C
24	Sv
25	F
26	C
27	S
28	H
29	V
30	ohm
31	J
32	N
33	Hz
34	lx
35	Lm
36	Wb
37	T
38	W
39	Pa
41	m ²
42	m ³
43	m/s
44	m/s ²
45	m ³ /s
46	m/m ³
47	M
48	kg/m ³
49	m ² /s
50	W/m K
51	J/K
52	ppm
53	1/s
54	rad/s
55	W/m ²
56	J/m ²
57	S/m
58	K/s
59	Pa/s
60	J/kg K
61	VA

Ordinal	Semantic
62	Watts
63	VAr
64	phi
65	cos(phi)
66	Vs
67	V ²
68	As
69	A ²
70	A ² t
71	VAh
72	Wh
73	VArh
74	V/Hz
75	Hz/s
76	char
77	char/s
78	kgm ²
79	dB
80	J/Wh
81	W/s
82	l/s
83	dBm
84	h
85	min

1.7.27 ENUMERATED TYPE: SWOPCAP

Description: Switch Operating Capability

Ordinal	Semantic
1	None
2	Open
3	Close
4	Open and Close

1.7.28 ENUMERATED TYPE: SWTYPE

Description: Switch Type

Ordinal	Semantic
1	Load Break
2	Disconnecter
3	Earthing Switch
4	High Speed Earthing Switch

1.7.29 ENUMERATED TYPE: WEEKDAY

Description: The Weekday

Ordinal	Semantic
0	reserved
1	Monday
2	Tuesday
3	Wednesday

Ordinal	Semantic
4	Thursday
5	Friday
6	Saturday
7	Sunday

1.8 MMS DATA-TYPE CONVERSIONS

The following table shows the relationships between the Part 7 and Part 8-1 data types. The definitions presented above use Part 7 data types, however these are subject to 'translation' when exposed over an MMS (Part 8-1) interface:

Part 7 Type	MMS Type	Part 7 Description
BOOLEAN	Bool	Logical TRUE/FALSE value
BSTR16	Bstring16	Bit-string -16 bits
BVstring13	BVstring13	Variable bit string (up to 13 bits)
Check	BVstring2	Control Object check flags
CODED_ENUM	Byte	Coded enumeration
CODED_ENUM2	Byte	Coded enumeration (2)
EntryTime	Btime6	8.1 Section 8.1.3.7
ENUMERATED16	Short	16 bit enumerated value
ENUMERATED32	Long	32 bit enumerated value
ENUMERATED8	Byte	8 bit enumerated value
FLOAT32	Float	32 bit floating point value
FLOAT64	Double	64 bit floating point value
INT128	Int64	128 bit signed integer value
INT16	Short	16 bit signed integer value
INT16U	Ushort	16 bit unsigned integer value
INT24U	Ulong	24 bit unsigned integer value
INT32	Long	32 bit signed integer value
INT32U	Ulong	32 bit unsigned integer value
INT64	Int64	64 bit signed integer value
INT8	Byte	8 bit signed integer value
INT8U	Ubyte	8 bit unsigned integer value
ObjectReference	Vstring129	Object Reference (129 character string)
OCTET_STRING6	Ostring6	6 character string (8 bits per character)
OCTET_STRING64	OVstring64	64 character string (8 bits per character)
OCTET_STRING8	OVstring8	8 character string (8 bits per character)
Quality	BVstring13	IEC61850 Quality
TimeStamp	Utctime	IEC61850 Time stamp
UNICODE_STRING255	UTF8Vstring255	255 character string (16 bits per unicode character)
UTC_TM	Utctime	UTC Timestamp
VISIBLE_STRING129	Vstring129	129 character string
VISIBLE_STRING255	Vstring255	255 character string
VISIBLE_STRING64	Vstring64	64 character string
VISIBLE_STRING65	Vstring65	65 character string
VISIBLE_STRING97	Vstring97	97 character string



GE VERNOVA